



# Unparalleled design integrity

## Advent Track

Advent can be mounted in a variety of surface or stem patterns, used vertically or horizontally on walls, and be cut in the field. Advent can also be used with Suspension Beam or Recessed Housings. Total track capacity is 40 amps when supplied by a 120/240V three-wire branch circuit. A choice of power feeds is available, all of which allow a variety of configurations powered at any point. For straight runs, order one 4-foot or 8-foot Individual Track section plus as many 8-foot Joiner Track sections as required including each straight run of track between intercepts.

### Benefits

- Variety of mounting patterns, surface or stems
- "U" shaped conductor provides reliable contact with connectors
- Can be cut in the field

### Features

- Total track capacity is 40 amps when supplied by a 120/240V three-wire branch circuit
- Available in 2', 4', 6', and 8' lengths

### Application

- Fashion
- Food and Large Retailers

## Advent Track

### Versions

