



Ideal general purpose downlight solution, providing comfortable quality light. Available in new construction and remodeler frame with interchangeable light engine that is offered in two lumen packages.

LyteCaster LED Downlight

Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

Benefits

- Comprehensive low cost IC family provides great value and visual performance

LyteCaster LED Downlight

Features

- 4,5,6" round and square
- Efficacy up to 90lm/W
- Lumens: 650-2000
- Wattage: 7-20W
- Voltage: 120V or 120V-277V

Application

- Residential
- Hospitality

Versions

