



Now with AccuRender LED Technology, LyteCaster provides comfortable quality light for new construction and remodeler frame with interchangeable light engines.

LyteCaster LED Downlight

Now with AccuRender LED Technology, LyteCaster provides comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes.

Benefits

- Comprehensive low cost IC family provides great value and visual performance

LyteCaster LED Downlight

Features

- 4,5,6" round and square
- Efficacy up to 103 lm/W
- Lumens: 650-2000
- Wattage: 7-20W
- Voltage: 120V or 120V-277V

Application

- Residential
- Hospitality
- Commercial
- Education
- Multi-Family Housing

Versions



L4R06830VA



L5R10RE1VA



LyteCaster LED Downlight

Versions

