



# Create efficiency in your design

## LyteProfile LED

LyteProfile LED downlights are designed for new construction and include downlight and wall wash distributions. They are highly energy efficient with up to 100 lm/w, provide a full 60 degree cutoff, and feature an impressively shallow 4.5" housing.

### Benefits

- Fixture depth remains below 4 1/2" deep and allows for a consistent 2" ceiling depth
- Innovative mid-flux LED design eliminates pixelation and provides smooth, even illumination with simplified thermal management
- The product line delivers up to 90 lm/W at the emitted luminaire level while providing a comfortable 60° cut-off to both the actual and reflected source

### Features

- Cutting edge technology employs the latest in thermal management and significantly reduces the size and physical material employed in the luminaire
- Designed to meet standard commercial lighting requirements with choices of 1000 lm, 1500 lm downlight or lensed wall wash in either a 4" or 6" apertures
- and up to 2000 lm in the 6" aperture
- Three component system design enables easy servicing plus upgradeability

### Application

- Office
- Banks
- Hospitality
- Airports
- Fashion

## LyteProfile LED

### Versions

