



EU Declaration of Conformity

Document Nr.: HU02-DoC-057-005

Year in which CE Mark was first affixed: 18

Manufacturer: Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

This declaration of conformity is issued under the sole responsibility of the manufacturer.

Product Range:	NAME: Coreline Downlight 3 DESCRIPTION: Recessed indoor luminaires for general purpose with LED modules
Product Code:	DN13XB (Details in Annex, see page 2 to 3)

The designated products are in conformity with the following Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Radio Equipment Directive (RED), 2014/53/EU (valid from 13th June 2016)

- EN 60598-1:2015 + AC:2015+AC:2016 Luminaires - Part 1: General requirements and tests
- EN 60598-2-2:2012 Luminaires - Part 2: Section 2 - Recessed luminaires
- EN 61347-1:2008 + A1:2011+A2:2013 Lamp control gear, General and safety requirements
- EN 62471:2008 Photobiological safety of lamps and lamp systems
- EN 301 489-1:2008-04 / V1.8.1
- EN 62493 :2010 Assessment of lighting equipment related to human exposure to electromagnetic fields (EMF)
- EN 55015:2013-08 (CISPR 15:2013 + IS1:2013 + IS2:2013) Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment
- EN 61547:2009 Equipment for general lighting purposes – EMC immunity requirements
- EN 61000-3-2:2014 Limits for Harmonic emissions (≤ 16 A per phase)
- EN 61000-3-3:2013 Limits - Limitation of voltage changes, voltage fluctuations and flicker in public low-voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subject to conditional connection
- ETSI EN 301 489-1 V1.9.2:2011-09 Electromagnetic compatibility and Radio Spectrum Matters (ERM); Electromagnetic Compatibility (EMC) standard for radio equipment and services
- ETSI EN 300 220-2 V3.1.1:2016 Short Range Devices (SRD) operating in the frequency range 25 MHz to 1 000 MHz

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- EC/244/2009 and amendment EC/859/2009
- EC/245/2009 and amendment EC/347/2010

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN 50581:2012 >> Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances

and are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Eindhoven, 09th March, 2018

High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Olaf von Bose

Industrial Q Manager Prof & Home
Product Quality

Philips Lighting



EU Declaration of Conformity

Specification of the products

10/12NC	EAN	Product Description	Remarks
910500457699	8718696852224	DN130B LED10S/830 PSU PI6 WH	
910500457701	8718696852231	DN130B LED10S/830 PSED-E II WH	
910500457702	8718696852248	DN130B LED20S/830 PSU PI6 WH	
910500457703	8718696852255	DN130B LED20S/830 PSED-E II WH	
910500457704	8718696852262	DN131B LED10S/830 PSU PI6 ALU	
910500457705	8718696852279	DN131B LED10S/830 PSED-E II ALU	
910500457706	8718696852286	DN131B LED20S/830 PSU PI6 ALU	
910500457707	8718696852293	DN131B LED20S/830 PSED-E II ALU	
910500457724	8718696852699	DN130B LED10S/840 PSU PI6 WH	
910500457725	8718696852705	DN130B LED10S/840 PSED-E II WH	
910500457726	8718696852712	DN130B LED20S/840 PSU PI6 WH	
910500457727	8718696852729	DN130B LED20S/840 PSED-E II WH	
910500457728	8718696852736	DN131B LED10S/840 PSU PI6 ALU	
910500457729	8718696852743	DN131B LED10S/840 PSED-E II ALU	
910500457730	8718696852750	DN131B LED20S/840 PSU PI6 ALU	
910500457731	8718696852767	DN131B LED20S/840 PSED-E II ALU	
910500458078	8718696878811	DN130B LED10S/830 PSU IP44 PI6 WH	
910500458079	8718696878828	DN130B LED10S/840 PSU IP44 PI6 WH	
910500458080	8718696878835	DN130B LED10S/830 PSED-E IP44 II WH	
910500458081	8718696878842	DN130B LED10S/840 PSED-E IP44 II WH	
910500458082	8718696878859	DN130B LED20S/830 PSU IP44 PI6 WH	
910500458083	8718696878866	DN130B LED20S/840 PSU IP44 PI6 WH	
910500458084	8718696878873	DN130B LED20S/830 PSED-E IP44 II WH	
910500458085	8718696878880	DN130B LED20S/840 PSED-E IP44 II WH	
910500458086	8718696878897	DN131B LED10S/830 PSU IP44 PI6 ALU	
910500458087	8718696878903	DN131B LED10S/840 PSU IP44 PI6 ALU	
910500458088	8718696878910	DN131B LED10S/830 PSED-E IP44 II ALU	
910500458089	8718696878927	DN131B LED10S/840 PSED-E IP44 II ALU	
910500458090	8718696878934	DN131B LED20S/830 PSU IP44 PI6 ALU	
910500458091	8718696878941	DN131B LED20S/840 PSU IP44 PI6 ALU	
910500458092	8718696878958	DN131B LED20S/830 PSED-E IP44 II ALU	
910500458093	8718696878965	DN131B LED20S/840 PSED-E IP44 II ALU	
910500458587	8718696913123	DN130B LED20S/830 PSED-E KIT	KIT
910500458587	8718696913130	DN130B LED20S/830 PSED-E KIT	KIT
910500458591	8718696913321	DN130B LED10S/830 PSED-E KIT	KIT
910500458591	8718696913352	DN130B LED10S/830 PSED-E KIT	KIT
910500458755	8718696916124	DN130B LED20S/830 PSED-E KIT 10PCS	KIT



EU Declaration of Conformity

910500458755	8718696916148	DN130B LED20S/830 PSED-E KIT 10PCS	KIT
910500458756	8718696916131	DN130B LED10S/830 PSED-E KIT 10PCS	KIT
910500458756	8718696916155	DN130B LED10S/830 PSED-E KIT 10PCS	KIT
910500458776	8718696916483	DN130B LED10S/840 PSED-E KIT	KIT
910500458776	8718696918883	DN130B LED10S/840 PSED-E KIT	KIT
910500458777	8718696916490	DN130B LED20S/840 PSED-E KIT	KIT
910500458777	8718696918876	DN130B LED20S/840 PSED-E KIT	KIT
910500458778	8718696916506	DN130B LED10S/830 IP PSED-E KIT	KIT
910500458778	8718699162887	DN130B LED10S/830 IP PSED-E KIT	KIT
910500458779	8718696916513	DN130B LED20S/830 IP PSED-E KIT	KIT
910500458779	8718699162894	DN130B LED20S/830 IP PSED-E KIT	KIT
910500458780	8718696916520	DN130B LED10S/840 IP PSED-E KIT	KIT
910500458780	8718699162900	DN130B LED10S/840 IP PSED-E KIT	KIT
910500458781	8718696916537	DN130B LED20S/840 IP PSED-E KIT	KIT
910500458781	8718699162917	DN130B LED20S/840 IP PSED-E KIT	KIT
910500458782	8718696916544	DN131B LED10S/830 PSED-E KIT	KIT
910500458782	8718696918890	DN131B LED10S/830 PSED-E KIT	KIT
910500458783	8718696916551	DN131B LED20S/830 PSED-E KIT	KIT
910500458783	8718696918906	DN131B LED20S/830 PSED-E KIT	KIT
910500458784	8718696916568	DN131B LED10S/840 PSED-E KIT	KIT
910500458784	8718696918913	DN131B LED10S/840 PSED-E KIT	KIT
910500458785	8718696916575	DN131B LED20S/840 PSED-E KIT	KIT
910500458785	8718696918920	DN131B LED20S/840 PSED-E KIT	KIT
910500458789	8718696916612	DN131B LED20S/840 IP PSED-E KIT	KIT
910500458789	8718699395964	DN131B LED20S/840 IP PSED-E KIT	KIT
910500465262	8718699397098	DN130B LED20S/830 IA1 WH	C4M version
910500465263	8718699397104	DN130B LED20S/840 IA1 WH	C4M version
910500465264	8718699397111	DN131B LED20S/830 IA1 ALU	C4M version
910500465265	8718699397128	DN131B LED20S/840 IA1 ALU	C4M version
910500465338	8718699400538	DN130B LED20S/830 IA1 WH EL3	C4M version
910500465339	8718699400545	DN130B LED20S/840 IA1 WH EL3	C4M version
910500465340	8718699400552	DN131B LED20S/830 IA1 ALU EL3	C4M version
910500465341	8718699400569	DN131B LED20S/840 IA1 ALU EL3	C4M version

– End of Annex –