



1F Specification Industrial

8', 3 Lamp F96T12HO, Painted Polyester Reflector, 10% Uplight

8', 3 Lamp F96T12HO, - Painted Polyester Reflector, 10% Uplight

The 1F Specification Industrial is a heavy duty industrial fluorescent luminaire providing 10% uplight and 13° crosswise sheilding.

Product data

General Information	
Lamp Envelope Code	T-12
Lamp Source Code	Fluorescent
Lamp Watts	110
Number of Lamps	3
Photometric Distribution Type	Semi Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	96 in

Shape	Linear
Product Data	
Order product name	8', 3 Lamp F96T12HO, Painted Polyester Reflector, 10% Uplight
Order code	1F396HO-PP
Material Nr. (12NC)	DAY00000008
Catalog Number	1F396HO-PP
Catalog Number Description	8', 3 Lamp F96T12HO, Painted Polyester Reflector, 10% Uplight