



DPWL Designer Wet Location

2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens

2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens

Designer Wet Location is a recessed luminare UL Listed for damp and wet locations (for covered ceiling use only).

Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	3
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V

Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Product Data	
Order product name	2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens
Order code	2DPWLG332-FS01-1/21-EB
Material Nr. (12NC)	DAY00000879
Catalog Number	2DPWLG332-FS01-1/21-EB
Catalog Number Description	2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens