



LBN Low Bay

1 Lamp 400wHPS, Acrylic Lens

1 Lamp 400wHPS, Acrylic Lens

The LBN Low Bay Luminaire offers the high efficiency general purpose industrial lighting for mounting height requirements of 30' and below.

Product data

General Information	
Lamp Envelope Code	BT/ED/E-18
Lamp Source Code	High Pressure Sodium
Lamp Watts	400
Number of Lamps	1
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Luminaire Input Watts	464

Mechanical and Housing	
Shape	Round
Product Data	
Order product name	1 Lamp 400wHPS, Acrylic Lens
Order code	LBN400S-CRA
Material Nr. (12NC)	DAY00003470
Catalog Number	LBN400S-CRA
Catalog Number Description	1 Lamp 400wHPS, Acrylic Lens