



DCL Designer Cleanroom

2x2, 2 Lamp 31U1T8, Clean Room, Pattern 12 .125" Thick Acrylic Lens

2x2, 2 Lamp 31U1T8, Clean Room, Pattern 12 .125" Thick Acrylic Lens

The Designer Clean Room is a recessed luminaire tested to federal standard 209E and designed for use with 1-1/2" face width inverted "T" bar ceilings.

Product data

General Information	
Lamp Envelope Code	T-8 Bent
Lamp Source Code	Fluorescent
Lamp Watts	31
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft

Product Data	
Order product name	2x2, 2 Lamp 31U1T8, Clean Room, Pattern 12 .125" Thick Acrylic Lens
Order code	2DCLG231U1-FA21-EB
Material Nr. (12NC)	DAY00007487
Catalog Number	2DCLG231U1-FA21-EB
Catalog Number Description	2x2, 2 Lamp 31U1T8, Clean Room, Pattern 12 .125" Thick Acrylic Lens