



FluxStream LED Wraparound

FluxStream Wraparound 4' 4000 LM 3500K UNV 0-10V DIM

FluxStream Wraparound 4' 4000 LM 3500K UNV 0-10V DIM

FluxStream LED wraparound is a high performing luminaire delivering smooth diffuse light ideal for light industrial, commercial and residential applications with the unparalleled energy efficiency of Philips LED lighting.

Product data

General information	
Connectivity	Interact Ready
Lamp Source Code	LED
Colour Temperature	3500 K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	Surface Wall Suspended
Buy American Compliant Products	Yes
Operating and electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	31
Mechanical and housing	
Fixture Size	48 in
Shape	Linear

Approval and application	
Energy Certifications	DLC Standard
Initial performance (IEC compliant)	
Luminaire Lumens	4000
Product data	
Order product name	FluxStream Wraparound 4' 4000 LM 3500K UNV 0-10V DIM
Order code	FSW440L835-UNV-DIM
Material Nr. (12NC)	DAY00008821
Catalog Number	FSW440L835-UNV-DIM
Catalog Number Description	FluxStream Wraparound 4' 4000 LM 3500K UNV 0-10V DIM