



FluxGrid Recessed LED

2x4 Base, 4200 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse

2x4 Base, 4200 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse – 118 lm/W

The Day-Brite / CFI Recessed FluxGrid LED offers architectural appeal with “must have” features. Two different lens styles, discrete air handling, integral emergency, and access to the boards and driver from below make FluxGrid an ideal solution for a wide range of applications.

Product data

General Information	
Colour Temperature	3500K
CRI	80
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	36
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Approval and Application	
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

Initial Performance (IEC Compliant)	
Luminaire Lumens	4200
Efficacy	118 lm/W
Product Data	
Order product name	2x4 Base, 4200 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse
Order code	2FGG42B835-4-D-UNV-DIM
Material Nr. (12NC)	DAY70000491
Catalog Number	2FGG42B835-4-D-UNV-DIM
Catalog Number Description	2x4 Base, 4200 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse

FluxGrid Recessed LED

