



# RBX LED High Bay

10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector

10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector - 129 lm/W

The RBX LED high bay luminaires have the familiar look and feel of traditional high bay luminaires. Available with acrylic or aluminum reflectors and a variety of lumen packages and color temperatures, the RBX is ideal for retail, industrial, and commercial applications.

## Product data

| General information             |                            |
|---------------------------------|----------------------------|
| Lamp Source Code                | LED                        |
| Colour Temperature              | 3500 K                     |
| CRI                             | 80                         |
| Photometric Distribution Type   | Direct                     |
| Mounting                        | Suspended                  |
| Buy American Compliant Products | Yes                        |
| Operating and electrical        |                            |
| Voltages                        | 120/208/240/277/347/UNIV V |
| Luminaire Input Watts           | 86                         |
| Mechanical and housing          |                            |
| Fixture Size                    | 22 in                      |
| Shape                           | Round                      |
| Approval and application        |                            |
| Energy Certifications           | DLC Standard               |

| Initial performance (IEC compliant) |   |
|-------------------------------------|---|
| Luminaire Lumens                    | 10000   |
| Efficacy                            | 129 lm/W  |
| Product data                        |   |
| Order product name                  | 10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector |
| Order code                          | RBX10L835-ARR22S  |
| Material Nr. (12NC)                 | DAY70000519   |
| Catalog Number                      | RBX10L835-ARR22S  |
| Catalog Number Description          | 10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector |

## RBX LED High Bay

