

BDS 798

Mounting instructions

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi


Οδηγίες συναρμολόγησης

Instrukcja montażu


Szerelési utasítások


Návod k montáži

Монтажная инструкция




BDS 798	830 W +/- 10%	740 W +/- 10%	840 W +/- 10%	LED	kg	max 25°C	m ²		
LED13	12.5	-	-	LED14	12.4	33	7.1	●	0.193m ²
LED26	24.5	-	-	LED28	24.4	66	7.2	●	0.193m ²
LED42	40.0	-	-	LED44	39.9	99	8.1	●	0.193m ²
GRN48	46.6	GRN49	45.2	-	-	32	8.1	●	0.193m ²
ECO46	48.4	ECO42	41.0	-	-	24	8.1	●	0.193m ²
ECO58	58.2	ECO57	53.2	-	-	32	8.1	●	0.193m ²
ECO70	71.5	ECO71	68.5	-	-	32	8.1	●	0.193m ²







2





LUMISTEP



DYNADIMMER



RF



D7 I-10V

Number of LED	GreenLine	EcoLine
24	OK only for 2-10V	
32	OK only for 2-10V	

