




LuxSpace G4筒灯
DN588/DN589/DN590/DN591/DN592/DN593/DN594调光筒灯
Mounting instruction/ 安装说明

444100006861




Type Number 产品型号	Cut Out 开孔尺寸	Lum. Power 整灯功率	Lamp Power 光源功率	Voltage 电压	Frequency 频率	Class 灯具类别	
DN588B	D100	8W	5.6W	220-240V	50/60Hz	II	0.38
DN589B	D125	10W	7.7W	220-240V	50/60Hz	II	0.45
DN589B	D150	10.5W	7.2W	220-240V	50/60HZ	II	0.45
DN590B	D125/150	13.8W	12W	220-240V	50/60HZ	I	0.45
DN591B	D125/150	20W	17W	220-240V	50/60Hz	I	0.45
DN591B	D200	17.5W	15.2W	220-240V	50/60Hz	I	1.40
DN592B	D150	23.3W	21.6W	220-240V	50/60Hz	I	0.80
DN593B	D200	30.8W	26.9W	220-240V	50/60Hz	I	1.40
DN594B	D200	39W	34.5W	220-240V	50/60Hz	I	1.40

Unit: mm
单位: 毫米



Type Number 产品型号	DN588B	DN588/DN589 /DN590/DN591	DN589/DN590/ DN591/DN592	DN593/ DN594
A(mm)	112	137	162	212
B(mm)	68	90	100	130
Cut Out	Ø100~105	Ø125~130	Ø152~157	Ø200~205




Unit: mm
单位: 毫米

Philips Lighting (China) Investment Co., Ltd.
Address: Building No. 9, Lane 888, Tianlin Road, Minhang District,
Shanghai, China Postal code: 200233
飞利浦照明(中国)投资有限公司
地址: 中国上海市闵行区田林路888弄9号楼
邮编: 200233



PHILIPS

2a




2b

↑
Pull
拉出




2c




3


↓
Push
推入




4




5



6




7



Type Number 产品型号	Cut Out 开孔尺寸	Inrush current	Duration	Inom
DN588B	D100/D125	16A	220us	41mA
DN589B	D125	16A	220us	49mA
DN589B	D150	16A	220us	51mA
DN590B	D125/D150	20.4A	195us	66mA
DN591B	D125/D150	20.4A	195us	94mA
DN591B	D200	20.4A	195us	83mA
DN592B	D150	20.4A	195us	108mA
DN593B	D200	20.4A	195us	141mA
DN594B	D200	20.4A	195us	179mA

IP54 (FRONT COVER WITH GLASS ONLY)

只有安装玻璃时出光面是IP54



- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装，接线要符合IEE电气标准或国家标准。
- The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.
此灯具不适合被隔热衬垫或类似材料覆盖
- Do not switch on before complete installation.
接线过程中，切勿通电。
- For non-user replaceable light sources:
对非使用者替换光源：
The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
此灯具内的光源应由制造商或其服务代理商或一个有类似资格的人来更换。
- The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc must be avoided during the use and storage.
灯具避免在腐蚀性环境或者含有有害物质，例如硫化物，卤化物，邻苯二甲酸酯等环境中存储和使用。
- For Class I luminaire MAX 24 Luminaires in one circuit
对于I类的灯具其环路安装的最大数量为24台