





PACIFIC WT360C/WT361C

Mounting instructions

Instructions de montage	Instrucciones de montaje	Kokoonpano- ja kiinnitysohjeet	Návod k montáži
Montageanleitung	Instruções de montagem	Montaj yönergesi	Návod k montáži
Montage instructie	Monteringsinstruktioner	Szerelési utasítások	
Istruzioni di montaggio	Monteringsvejledning	Instrukcja montażu	





~220V...240V
50 Hz/60 Hz



max
ta
+35°C

min
ta
-30°C



min
30 cm







TC



service

