



Structural Components

Poles, Bases, Arms and Accessories

PHILIPS
HABCO



Simply enhancing life with light

Since 1953, we've built our products to a superior standard of quality and craftsmanship, using only the finest raw materials and components available. We've also built our business to a superior standard of consistency and reliability.

We inspect every piece we manufacture, multiple times, for fit and finish. Each of our designs is precision engineered, backed by ISO 9001 Certification. And our comprehensive warranties exceed industry standards.

But that doesn't entirely explain how we became the industry leader. There's another important area where we excel.

Service.

Smart. Prompt. And flexible.

At Philips Hadco, it has to be – because we provide the broadest selection of styles, finishes, and lamping options in the industry. Our superior service helps you navigate the choices and ensures that you're getting just what you need. When you need it. Even if we have to custom design it.


When you light with Philips Hadco, you can rest assured it'll be done right. On time.

That's why more and more architects and designers depend on Philips Hadco. Because they know what they'll get. Satisfaction.

Poles

Contents


P100 Series	1
P295 Series	3
P1150 Series	5
P1500 Series	7
P1600 Series	11
P1700 Series	13
P1900 Series	15
P2000 Series	17
P2100 Series	21
P2500 Series	23
P3100 Series	27
P4000 Series	29
P4100 Series	31
P4400 Series	33
P5000 Series	35
P5100 Series	37
P8000 Series	39
P9000 Series	41
PSPT Series	43







Shown: Pole P150, Custom Fixture.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft. (P170 is made of low carbon steel base, 7 ga. hot rolled steel.)

Ordering Example: **P170 10 B**


PRODUCT CODE TENON/TOP	P120 3" O.D.	P150 3" O.D.	P170 4" O.D.	P195 4" O.D.
(BASE TEMPLATE)				
BOLT CIRCLE	7 1/2" – 9 1/2" dia.	7" dia.	7" – 11" dia.	7 1/2" – 9 1/2" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(3) 1/2" dia. x 15 1/2" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	11 1/2" dia. x 2 3/8" H	9-5/8" dia. x 1 3/8" H	13" x 3/4" Plate	11 1/2" dia. x 2 3/8" H
BASE COVER (INCLUDED)	12 1/8" dia. x 3 1/4" H	10-1/4" dia. x 2 3/4" H	13 1/2" dia. x 3" H	12 1/8" dia. x 3 1/4" H
HAND-HOLE OPENING	2" x 4" Oval	2" x 4" Oval	2" x 4" Oval	2" x 4" Oval
SHAFT	4" to 3" Tapered	3" Straight	4" Straight	4" Straight
WALL	0.125 Aluminum	0.125 Aluminum	7 ga. Steel	0.188 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH 8' 9.78 6.10 10' 7.85 4.82 12' 6.45 3.60 14' 4.11 2.01	HT. 80 MPH 100 MPH 8' 3.19 1.80 10' 2.19 1.07	HT. 80 MPH 100 MPH 10' 43.32 27.22 12' 36.30 22.62 14' 24.80 15.29 16' 21.40 13.00 18' 18.62 11.11 20' 16.28 9.50	HT. 80 MPH 100 MPH 12' 6.45 3.88 14' 4.13 2.31 15' 3.92 2.01 16' 3.35 1.80 18' 2.72 1.34 20' 2.17 0.93

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P100 Series Poles, please visit www.hadco.com. Search by product name or number.




Shown: Pole P295, Fixture Custom.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: P295 12 B


PRODUCT CODE	P295		
TENON/TOP	4" SQUARE		
(BASE TEMPLATE)			
BOLT CIRCLE	9 1/2" dia.		
ANCHOR RODS	(4) 3/4" dia. x 19" L		
BASE	11 1/2" sq. x 2" H		
BASE COVER (INCLUDED)	17 5/16" sq. x 3 1/4" H		
HAND -HOLE OPENING	2" x 4" Oval		
SHAFT	4" Straight		
WALL	0.188 Aluminum		
HEIGHT/EPA WIND ZONE*	HT.	80 MPH	100 MPH
	12'	17.52	10.29
	14'	11.56	6.52
	15'	10.21	5.65
	16'	9.49	5.02
	18'	7.74	3.73
	20'	6.23	2.60

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on the P295, please visit www.hadco.com. Search by product name or number.



Shown: Pole P1150, Fixture V600 modified with frosted glass chimney.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P1150 86 B**



PRODUCT CODE	P1150		
TENON/TOP	3" O.D.		
(BASE TEMPLATE)			
BOLT CIRCLE	7" dia.		
ANCHOR RODS	(4) 1/2" dia. x 15" L		
BASE	11" dia. x 30" H		
BASE COVER	Internal Anchor Rods		
HAND -HOLE OPENING	4 1/4" x 4 1/2"		
SHAFT	4" to 3" Tapered		
WALL	0.125 Aluminum		
HEIGHT/EPA WIND ZONE*	HT.	80 MPH	100 MPH
	8' 6"	9.06	5.42
	10' 6"	7.06	4.03
	12' 6"	5.55	2.95

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on the P1150, please visit www.hadco.com. Search by product name or number.



Shown: Pole P1521, Fixture V092.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P1511 10 H**



PRODUCT CODE TENON/TOP	P1511 3" O.D.	P1521 3" O.D.	P1561 3" O.D.
(BASE TEMPLATE)			
BOLT CIRCLE	9 3/8" dia.	9 3/8" dia.	9 3/8" dia.
ANCHOR RODS	(4) 1/2" dia. x 15 1/2" L	(4) 1/2" dia. x 15 1/2" L	(4) 1/2" dia. x 15 1/2" L
BASE	8 1/4" sq. x 27 3/8" H	8 1/4" sq. x 27 3/8" H	8 1/4" sq. x 27 3/8" H
BASE COVER (INCLUDED)	9" sq. x 3" H	9" sq. x 3" H	9" sq. x 3" H
HAND-HOLE OPENING	3" x 5"	3" x 5"	3" x 5"
SHAFT	3" Straight	4" to 3" Tapered	3" Straight Fluted
WALL	0.125 Aluminum	0.125 Aluminum up to 12' 0.188 Aluminum 14'	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH 8' 9.99 5.84 10' 8.02 4.60 12' 6.64 3.72	HT. 80 MPH 100 MPH 8' 10.24 5.78 10' 8.12 4.44 12' 6.64 3.50 14' 7.57 4.26	HT. 80 MPH 100 MPH 8' 9.77 5.72 10' 7.85 4.51 12' 6.50 3.65

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P1500 Series Poles, please visit www.hadco.com. Search by product name or number.






Shown: Pole P1516, Fixture V092.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P1526 12 A**

PRODUCT CODE TENON/TOP	P1516 3" O.D.	P1526 3" O.D.	P1566 3" O.D.
(BASE TEMPLATE)			
	Base: 8 1/4"	Base: 8 1/4"	Base: 8 1/4"
	Base Cover: 12 3/4"	Base Cover: 12 3/4"	Base Cover: 12 3/4"
BOLT CIRCLE	9 3/8" dia.	9 3/8" dia.	9 3/8" dia.
ANCHOR RODS	(4) 1/2" dia. x 15 1/2" L	(4) 1/2" dia. x 15 1/2" L	(4) 1/2" dia. x 15 1/2" L
BASE	8 1/4" sq. x 27 3/8" H	8 1/4" sq. x 27 3/8" H	8 1/4" sq. x 27 3/8" H
BASE COVER (INCLUDED)	12 3/4" dia. x 5 1/2" H	12 3/4" dia. x 5 1/2" H	12 3/4" dia. x 5 1/2" H
HAND-HOLE OPENING	3" x 5"	3" x 5"	3" x 5"
SHAFT	3" Straight	4" x 3" Tapered	3" Straight Fluted
WALL	0.125 Aluminum	0.125 Aluminum up to 12' 0.188 Aluminum 14'	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	8' 9.99 5.84	8' 10.24 5.78	8' 9.77 5.72
	10' 8.02 4.60	10' 8.12 4.44	10' 7.85 4.51
	12' 6.64 3.72	12' 6.64 3.50	12' 6.50 3.65
		14' 7.57 4.26	


*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P1500 Series Poles, please visit www.hadco.com. Search by product name or number.

P1600





Shown: Pole P1610, Arm HFP510, Fixture TF2.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P1610 14 B**


PRODUCT CODE	P1600			P1610		
TENON/TOP	3" O.D.			4" O.D.		
(BASE TEMPLATE)						
BOLT CIRCLE	8"–13" dia.			8"–13" dia.		
ANCHOR RODS	(4) 3/4" dia. x 19" L			(4) 3/4" dia. x 19" L		
BASE	16" dia. x 22" H			16" dia. x 22" H		
BASE COVER (INCLUDED)	Internal Anchor Rods			Internal Anchor Rods		
HAND -HOLE OPENING	9" x 10"			9" x 10"		
SHAFT	4" x 3" Smooth Tapered			4" Smooth Straight		
WALL	0.125 Aluminum			0.125 Aluminum		
HEIGHT/EPA WIND ZONE*	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH
	10'	12.53	7.52	8'	12.53	7.52
	12'	10.08	5.84	12'	10.08	5.84
	14'	6.53	3.60	14'	6.53	3.60
	16'	5.21	2.64	16'	5.21	2.64

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P1600 Series Poles, please visit www.hadco.com. Search by product name or number.






Shown: Pole P1791, Fixture V651.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P1711 128 A**


PRODUCT CODE TENON/TOP	P1711 3" O.D.	P1761 3" O.D.	P1791 3" O.D.																																													
(BASE TEMPLATE)	 Base: 10 1/2" Base Cover: 11 1/2" sq. 16 1/4" Point to Point	 Base: 10 1/2" Base Cover: 11 1/2" sq. 16 1/4" Point to Point	 Base: 10 1/2" Base Cover: 11 1/2" sq. 16 1/4" Point to Point																																													
BOLT CIRCLE	11 3/8" x 12 3/4" dia.	11 3/8" x 12 3/4" dia.	11 3/8" x 12 3/4" dia.																																													
ANCHOR RODS	(4) 5/8" dia. x 15 3/8" L	(4) 5/8" dia. x 15 3/8" L	(4) 5/8" dia. x 15 3/8" L																																													
BASE	10 1/2" sq. x 22" H	10 1/2" sq. x 49" H	10 1/2" sq. x 49" H																																													
BASE COVER (INCLUDED)	11 1/2" sq. x 2 1/2" H	11 1/2" sq. x 2 1/2" H	11 1/2" sq. x 2 1/2" H																																													
HAND-HOLE OPENING	7 1/2" x 4"	7 1/2" x 4"	7 1/2" x 4"																																													
SHAFT	5" to 3" Tapered	4" Straight Fluted	4" to 3" Tapered																																													
WALL	0.125 Aluminum	0.125 Aluminum	0.125 Aluminum																																													
HEIGHT/EPA WIND ZONE*	<table><tr><th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr><tr><td>10' 8"</td><td>24.75</td><td>15.39</td></tr><tr><td>12' 8"</td><td>16.28</td><td>9.88</td></tr><tr><td>14' 8"</td><td>13.74</td><td>8.16</td></tr><tr><td>16' 8"</td><td>11.65</td><td>6.71</td></tr></table>	HT.	80 MPH	100 MPH	10' 8"	24.75	15.39	12' 8"	16.28	9.88	14' 8"	13.74	8.16	16' 8"	11.65	6.71	<table><tr><th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr><tr><td>10'</td><td>8.54</td><td>4.99</td></tr><tr><td>12'</td><td>6.86</td><td>3.83</td></tr><tr><td>14'</td><td>4.08</td><td>1.97</td></tr><tr><td>16'</td><td>3.10</td><td>1.23</td></tr></table>	HT.	80 MPH	100 MPH	10'	8.54	4.99	12'	6.86	3.83	14'	4.08	1.97	16'	3.10	1.23	<table><tr><th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr><tr><td>10'</td><td>8.54</td><td>4.99</td></tr><tr><td>12'</td><td>6.86</td><td>3.83</td></tr><tr><td>14'</td><td>4.08</td><td>1.97</td></tr><tr><td>16'</td><td>3.10</td><td>1.23</td></tr></table>	HT.	80 MPH	100 MPH	10'	8.54	4.99	12'	6.86	3.83	14'	4.08	1.97	16'	3.10	1.23
HT.	80 MPH	100 MPH																																														
10' 8"	24.75	15.39																																														
12' 8"	16.28	9.88																																														
14' 8"	13.74	8.16																																														
16' 8"	11.65	6.71																																														
HT.	80 MPH	100 MPH																																														
10'	8.54	4.99																																														
12'	6.86	3.83																																														
14'	4.08	1.97																																														
16'	3.10	1.23																																														
HT.	80 MPH	100 MPH																																														
10'	8.54	4.99																																														
12'	6.86	3.83																																														
14'	4.08	1.97																																														
16'	3.10	1.23																																														

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P1700 Series Poles, please visit www.hadco.com. Search by product name or number.





Shown: Pole P1910, Fixture V671.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P1910 126 H**


PRODUCT CODE	P1910	P1950
TENON/TOP	3" O.D.	3" O.D.
(BASE TEMPLATE)		
	Base: 12 1/4"	Base: 12 1/4"
BOLT CIRCLE	7" - 9 1/2" dia.	7" - 9 1/2" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	12 1/4" dia. x 20 3/4" H	12 1/4" dia. x 41" H
BASE COVER	Internal Anchor Rods	Internal Anchor Rods
HAND -HOLE OPENING	7" x 9"	7" x 9"
SHAFT	4" to 3" Smooth Tapered	4" to 3" Tapered
WALL	0.125 Aluminum	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	8' 6" 12.67 7.82	10' 8.54 4.99
	10' 6" 9.67 5.79	12' 6.86 3.83
	12' 6" 7.57 4.34	14' 4.08 1.97
	14' 6" 4.79 2.58	16' 3.10 1.23

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P1900 Series Poles, please visit www.hadco.com. Search by product name or number.



Shown: Pole P2060, Fixture R52GANN.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P2061 14 A**


PRODUCT CODE TENON/TOP	P2025 3" O.D.	P2060 3" O.D.	P2061 3" O.D.
(BASE TEMPLATE)	 Base: 16"	 Base: 16"	 Base: 16"
BOLT CIRCLE	8" to 12" dia.	12" dia.	8" to 12" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	16" dia. x 21" H	16" dia. x 21" H	16" dia. x 21" H
BASE COVER	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods
HAND -HOLE OPENING	5" x 8"	5" x 8"	5" x 8"
SHAFT	5" to 3" Tapered	4" Straight Fluted	4" Straight Fluted
WALL	0.125 Aluminum up to 12' 0.188 Aluminum 14' and up	0.125 Aluminum	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	10' 14.91 8.83	10' 8.23 4.47	10' 11.29 6.17
	12' 12.43 7.25	12' 6.71 3.51	12' 9.21 4.85
	14' 12.04 6.93	14' 4.46 2.24	14' 6.13 3.09
	16' 9.90 5.38		16' 4.62 1.93

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P2000 Series Poles, please visit www.hadco.com. Search by product name or number.






Shown: Pole P2060, Fixture R52BDGC.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: P2065 12 H


PRODUCT CODE	P2063	P2065	P2071
TENON/TOP	3" O.D.	3" O.D.	3" O.D.
(BASE TEMPLATE)			
BOLT CIRCLE	8" to 12" dia.	8" to 12" dia.	8" to 12" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	16" dia. x 21" H	16" dia. x 21" H	16" dia. x 21" H
BASE COVER	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods
HAND -HOLE OPENING	5" x 8"	5" x 8"	5" x 8"
SHAFT	4" Straight Flat Fluted	5" Straight Flat Fluted	4" Straight Fluted
WALL	0.188 – 0.313 Aluminum	0.188 – 0.267 Aluminum	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	10' 19.19 11.29	10' 25.34 15.00	10' 12.29 6.74
	12' 15.96 9.23	12' 21.11 12.30	12' 10.14 5.41
	14' 10.85 6.16	14' 14.38 8.24	14' 6.83 3.54
	16' 8.84 4.69	16' 11.78 6.34	16' 5.34 2.42

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P2000 Series Poles, please visit www.hadco.com. Search by product name or number.





Shown: Pole P2165, Fixture: Modified T03.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P2165 16 B**


PRODUCT CODE	P2165			P2170		
TENON/TOP	3" O.D.			3" O.D.		
(BASE TEMPLATE)						
BOLT CIRCLE	8" to 17" dia.			8" to 17" dia.		
ANCHOR RODS	(4) 3/4" dia. x 19" L			(4) 3/4" dia. x 19" L		
BASE	20" dia. x 25 3/8" H			20" dia. x 25 3/8" H		
BASE COVER	Internal Anchor Rods			Internal Anchor Rods		
HAND -HOLE OPENING	11" x 16"			11" x 16"		
SHAFT	5" Straight Flat Fluted			5" to 3" Tapered		
WALL	0.188–0.267 Aluminum			0.125 Aluminum up to 12' 0.188 Aluminum 14' and up		
HEIGHT/EPA WIND ZONE [*]	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH
	12'	18.42	10.56	12'	12.81	7.47
	14'	12.51	7.03	14'	13.15	7.51
	16'	10.15	5.29	16'	10.78	5.79
	18'	8.78	4.43	18'	9.38	4.90

^{*}EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P2100 Series Poles, please visit www.hadco.com. Search by product name or number.



Shown: Pole P2560, Fixture V25 modified with solid roof and custom finial.



Ordering Guide


- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P170 10 B**

PRODUCT CODE TENON/TOP	P2520 3" O.D.	P2540 3" O.D.																														
(BASE TEMPLATE)	Base: 12 3/4" Base Cover: 14" sq. 19 3/4" Point to Point	Base: 12 3/4" Base Cover: 14" sq. 19 3/4" Point to Point																														
BOLT CIRCLE	11" to 14" dia.	11" to 14" dia.																														
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L																														
BASE	12 3/4" sq. x 43 3/4" H	12 3/4" sq. x 44 3/8" H																														
BASE COVER (INCLUDED)	14" sq. x 4 3/4" H	14" sq. x 4 3/4" H																														
HAND-HOLE OPENING	4 3/8" x 5 3/4"	4 3/8" x 5 3/4"																														
SHAFT	5" to 3" Tapered	4" Straight Flat Fluted																														
WALL	0.125 Aluminum	0.188–0.313 Aluminum																														
HEIGHT/EPA WIND ZONE*	<table> <tr> <th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr> <tr> <td>10'</td><td>27.80</td><td>17.27</td></tr> <tr> <td>12'</td><td>22.89</td><td>14.02</td></tr> <tr> <td>14'</td><td>15.29</td><td>9.19</td></tr> <tr> <td>16'</td><td>12.76</td><td>7.46</td></tr> </table>	HT.	80 MPH	100 MPH	10'	27.80	17.27	12'	22.89	14.02	14'	15.29	9.19	16'	12.76	7.46	<table> <tr> <th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr> <tr> <td>10'</td><td>13.78</td><td>8.34</td></tr> <tr> <td>12'</td><td>11.22</td><td>6.60</td></tr> <tr> <td>14'</td><td>6.97</td><td>3.77</td></tr> <tr> <td>16'</td><td>5.54</td><td>2.72</td></tr> </table>	HT.	80 MPH	100 MPH	10'	13.78	8.34	12'	11.22	6.60	14'	6.97	3.77	16'	5.54	2.72
HT.	80 MPH	100 MPH																														
10'	27.80	17.27																														
12'	22.89	14.02																														
14'	15.29	9.19																														
16'	12.76	7.46																														
HT.	80 MPH	100 MPH																														
10'	13.78	8.34																														
12'	11.22	6.60																														
14'	6.97	3.77																														
16'	5.54	2.72																														

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P2500 Series Poles, please visit www.hadco.com. Search by product name or number.



Ordering Guide


- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P2550 12 A**

PRODUCT CODE TENON/TOP	P2550 3" O.D.	P2560 3" O.D.																														
(BASE TEMPLATE)																																
BOLT CIRCLE	11" to 14" dia.	11" to 14" dia.																														
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L																														
BASE	12 3/4" sq. x 43 3/4" H	12 3/4" sq. x 44 3/8" H																														
BASE COVER (INCLUDED)	14" sq. x 4 3/4" H	14" sq. x 4 3/4" H																														
HAND-HOLE OPENING	4 3/8" x 5 3/4"	4 3/8" x 5 3/4"																														
SHAFT	5" Straight Flat Fluted	4" Straight Fluted																														
WALL	0.188 - 0.267 Aluminum	0.125 Aluminum																														
HEIGHT/EPA WIND ZONE*	<table> <tr> <th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr> <tr> <td>12'</td><td>23.42</td><td>14.48</td></tr> <tr> <td>14'</td><td>15.29</td><td>9.19</td></tr> <tr> <td>16'</td><td>12.76</td><td>7.46</td></tr> <tr> <td>18'</td><td>10.65</td><td>5.99</td></tr> </table>	HT.	80 MPH	100 MPH	12'	23.42	14.48	14'	15.29	9.19	16'	12.76	7.46	18'	10.65	5.99	<table> <tr> <th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr> <tr> <td>10'</td><td>13.78</td><td>8.34</td></tr> <tr> <td>12'</td><td>11.22</td><td>6.60</td></tr> <tr> <td>14'</td><td>6.97</td><td>3.77</td></tr> <tr> <td>16'</td><td>5.54</td><td>2.72</td></tr> </table>	HT.	80 MPH	100 MPH	10'	13.78	8.34	12'	11.22	6.60	14'	6.97	3.77	16'	5.54	2.72
HT.	80 MPH	100 MPH																														
12'	23.42	14.48																														
14'	15.29	9.19																														
16'	12.76	7.46																														
18'	10.65	5.99																														
HT.	80 MPH	100 MPH																														
10'	13.78	8.34																														
12'	11.22	6.60																														
14'	6.97	3.77																														
16'	5.54	2.72																														

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P2500 Series Poles, please visit www.hadco.com. Search by product name or number.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: P2555 12 H


PRODUCT CODE	P2525	P2555	P2565
TENON/TOP	3" O.D.	3" O.D.	3" O.D.
(BASE TEMPLATE)			
BOLT CIRCLE	11" to 14" dia.	11" to 14" dia.	11" to 14" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	12 3/4" sq. x 43 3/4" H	12 3/4" sq. x 43 3/4" H	12 3/4" sq. x 43 3/4" H
BASE COVER (INCLUDED)	19" dia. x 9 1/4" H	19" dia. x 9 1/4" H	19" dia. x 9 1/4" H
HAND-HOLE OPENING	4 3/8" x 5 3/4"	4 3/8" x 5 3/4"	4 3/8" x 5 3/4"
SHAFT	5" to 3" Tapered	5" Straight Flat Fluted	4" Straight Fluted
WALL	0.125 Aluminum	0.188-0.267 Aluminum	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH 10' 27.80 17.27 12' 22.89 14.02 14' 15.29 9.19 16' 12.76 7.46	HT. 80 MPH 100 MPH 12' 23.42 14.48 14' 15.29 9.19 16' 12.76 7.46 18' 10.65 5.99	HT. 80 MPH 100 MPH 10' 13.78 8.34 12' 11.22 6.60 14' 6.97 3.77 16' 5.54 2.72

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P2500 Series Poles, please visit www.hadco.com. Search by product name or number.





Shown: Pole P3165, Fixture R54TABB.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P3165 14 B**


PRODUCT CODE	P3120			P3165		
TENON/TOP	3" O.D.			3" O.D.		
(BASE TEMPLATE)						
BOLT CIRCLE	8" to 13" dia.			8" to 13" dia.		
ANCHOR RODS	(4) 3/4" dia. x 19" L			(4) 3/4" dia. x 19" L		
BASE	17" dia. x 29" H			17" dia. x 29" H		
BASE COVER	Internal Anchor Rods			Internal Anchor Rods		
HAND -HOLE OPENING	4" x 7 1/2"			4" x 7 1/2"		
SHAFT	5" to 3" Tapered			5" Straight Flat Fluted		
WALL	0.125 Aluminum up to 12' 0.188 Aluminum 14' and up			0.188 – 0.267 Aluminum		
HEIGHT/EPA WIND ZONE*	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH
	12'	13.77	8.09	12'	36.78	22.32
	14'	13.55	7.77	14'	25.32	15.24
	16'	11.14	6.02	16'	21.51	12.59
	18'	9.71	5.11	18'	18.99	10.98

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P3100 Series Poles, please visit www.hadco.com. Search by product name or number.






Shown: Pole P4030 modified with receptacle. Custom Hadco Arm. Fixture CF2.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P4031 16 B**


PRODUCT CODE	P4020	P4030	P4031																																													
TENON/TOP	3" O.D.	3" O.D.	4" O.D.																																													
(BASE TEMPLATE)																																																
BOLT CIRCLE	8" to 12" dia.	8" to 12" dia.	8" to 12" dia.																																													
ANCHOR RODS	(4) 3/4" DIA. x 19" L	(4) 3/4" DIA. x 19" L	(4) 3/4" DIA. x 19" L																																													
BASE	15" dia. x 46 1/8" H	15" dia. x 46 1/8" H	15" dia. x 46 1/8" H																																													
BASE COVER	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods																																													
HAND -HOLE OPENING	6" x 12"	6" x 12"	6" x 12"																																													
SHAFT	5" to 3" Tapered	4" Straight	4" Straight																																													
WALL	0.125 Aluminum	0.125 Aluminum	0.125 Aluminum																																													
HEIGHT/EPA WIND ZONE*	<table><tr><th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr><tr><td>12'</td><td>18.69</td><td>11.61</td></tr><tr><td>14'</td><td>12.16</td><td>7.38</td></tr><tr><td>16'</td><td>10.11</td><td>6.00</td></tr><tr><td>18'</td><td>8.40</td><td>4.83</td></tr></table>	HT.	80 MPH	100 MPH	12'	18.69	11.61	14'	12.16	7.38	16'	10.11	6.00	18'	8.40	4.83	<table><tr><th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr><tr><td>12'</td><td>18.69</td><td>11.61</td></tr><tr><td>14'</td><td>12.16</td><td>7.38</td></tr><tr><td>16'</td><td>10.11</td><td>6.00</td></tr><tr><td>18'</td><td>8.40</td><td>4.83</td></tr></table>	HT.	80 MPH	100 MPH	12'	18.69	11.61	14'	12.16	7.38	16'	10.11	6.00	18'	8.40	4.83	<table><tr><th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr><tr><td>12'</td><td>18.69</td><td>11.61</td></tr><tr><td>14'</td><td>12.16</td><td>7.38</td></tr><tr><td>16'</td><td>10.11</td><td>6.00</td></tr><tr><td>18'</td><td>8.40</td><td>4.83</td></tr></table>	HT.	80 MPH	100 MPH	12'	18.69	11.61	14'	12.16	7.38	16'	10.11	6.00	18'	8.40	4.83
HT.	80 MPH	100 MPH																																														
12'	18.69	11.61																																														
14'	12.16	7.38																																														
16'	10.11	6.00																																														
18'	8.40	4.83																																														
HT.	80 MPH	100 MPH																																														
12'	18.69	11.61																																														
14'	12.16	7.38																																														
16'	10.11	6.00																																														
18'	8.40	4.83																																														
HT.	80 MPH	100 MPH																																														
12'	18.69	11.61																																														
14'	12.16	7.38																																														
16'	10.11	6.00																																														
18'	8.40	4.83																																														

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P4000 Series Poles, please visit www.hadco.com. Search by product name or number.






Shown: Pole P4130, Fixture CF7P.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P4130 12 A**


PRODUCT CODE	P4120	P4130	P4131
TENON/TOP	3" O.D.	3" O.D.	4" O.D.
(BASE TEMPLATE)			
BOLT CIRCLE	8" to 14" dia.	8" to 14" dia.	8" to 14" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	19" dia. x 54 1/2" H	19" dia. x 54 1/2" H	19" dia. x 54 1/2" H
BASE COVER	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods
HAND -HOLE OPENING	6" x 11 1/2"	6" x 11 1/2"	6" x 11 1/2"
SHAFT	5" to 3" Tapered	4" Straight	4" Straight
WALL	0.125 Aluminum	0.125 Aluminum	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	12' 15.28 9.33	12' 16.74 10.26	12' 16.74 10.26
	14' 9.88 5.78	14' 10.90 6.43	14' 10.90 6.43
	16' 8.16 4.56	16' 9.07 5.13	16' 9.07 5.13
	18' 6.72 3.51	18' 7.53 4.03	18' 7.53 4.03

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P4100 Series Poles, please visit www.hadco.com. Search by product name or number.





Shown: Pole P4465, Fixture V600.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P4420 14 H**


PRODUCT CODE	P4420	P4465																														
TENON/TOP	3" O.D.	3" O.D.																														
(BASE TEMPLATE)																																
BOLT CIRCLE	8" to 12" dia.	8" to 12" dia.																														
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L																														
BASE	15 1/2" dia. x 48" H	15 1/2" dia. x 48" H																														
BASE COVER	Internal Anchor Rods	Internal Anchor Rods																														
HAND -HOLE OPENING	11" x 5"	11" x 5"																														
SHAFT	5" to 3" Tapered	5" Straight Flat Fluted																														
WALL	0.125 Aluminum	0.188 - 0.267 Aluminum																														
HEIGHT/EPA WIND ZONE*	<table> <tr> <th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr> <tr> <td>12'</td><td>23.29</td><td>14.40</td></tr> <tr> <td>14'</td><td>15.21</td><td>9.14</td></tr> <tr> <td>16'</td><td>12.69</td><td>7.41</td></tr> <tr> <td>18'</td><td>10.59</td><td>5.95</td></tr> </table>	HT.	80 MPH	100 MPH	12'	23.29	14.40	14'	15.21	9.14	16'	12.69	7.41	18'	10.59	5.95	<table> <tr> <th>HT.</th><th>80 MPH</th><th>100 MPH</th></tr> <tr> <td>12'</td><td>23.29</td><td>14.40</td></tr> <tr> <td>14'</td><td>15.21</td><td>9.14</td></tr> <tr> <td>16'</td><td>12.69</td><td>7.41</td></tr> <tr> <td>18'</td><td>10.59</td><td>5.95</td></tr> </table>	HT.	80 MPH	100 MPH	12'	23.29	14.40	14'	15.21	9.14	16'	12.69	7.41	18'	10.59	5.95
HT.	80 MPH	100 MPH																														
12'	23.29	14.40																														
14'	15.21	9.14																														
16'	12.69	7.41																														
18'	10.59	5.95																														
HT.	80 MPH	100 MPH																														
12'	23.29	14.40																														
14'	15.21	9.14																														
16'	12.69	7.41																														
18'	10.59	5.95																														

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P4400 Series Poles, please visit www.hadco.com. Search by product name or number.






Shown: Pole 5020, Fixture V681 with a custom finial.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: P5020 14 A


PRODUCT CODE	P5020	P5065	P5092
TENON/TOP	3" O.D.	3" O.D.	3" O.D.
(BASE TEMPLATE)			
BOLT CIRCLE	8" to 13" dia.	8" to 13" dia.	8" to 13" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	17" dia. x 21" H	17" dia. x 21" H	17" dia. x 21" H
BASE COVER	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods
HAND -HOLE OPENING	4 1/2" x 5"	4 1/2" x 5"	4 1/2" x 5"
SHAFT	5" to 3" Tapered	5" Straight Flat Fluted	6" to 4" Tapered Fluted
WALL	0.125 Aluminum up to 12' 0.188 Aluminum 14' and up	0.188 - 0.267 Aluminum	0.188 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	12' 13.77 8.12	12' 28.22 16.70	12' 20.55 12.12
	14' 9.40 5.47	14' 19.29 11.26	14' 14.03 8.16
	16' 7.79 4.30	16' 16.00 8.89	16' 11.61 6.41
	18' 6.80 3.67	18' 13.99 7.60	

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P5000 Series Poles, please visit www.hadco.com. Search by product name or number.




Shown: Pole P5191, Fixture V092.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P5164 16 B**


PRODUCT CODE	P5164			P5165			P5170			P5192		
TENON/TOP	3" O.D.			3" O.D.			3" O.D.			3" O.D.		
(BASE TEMPLATE)												
BOLT CIRCLE	10" to 15" dia.			10" to 15" dia.			10" to 15" dia.			10" to 15" dia.		
ANCHOR RODS	(4) 3/4" dia. x 19" L			(4) 3/4" dia. x 19" L			(4) 3/4" dia. x 19" L			(4) 3/4" dia. x 19" L		
BASE	20" dia. x 23 3/4" H			20" dia. x 23 3/4" H			20" dia. x 23 3/4" H			20" dia. x 23 3/4" H		
BASE COVER	Internal Anchor Rods			Internal Anchor Rods			Internal Anchor Rods			Internal Anchor Rods		
HAND-HOLE OPENING	4 1/2" x 5"			4 1/2" x 5"			4 1/2" x 5"			4 1/2" x 5"		
SHAFT	4" Straight Flat Fluted			5" Straight Flat Fluted			5" to 3" Tapered			6" to 4" Tapered Fluted		
WALL	0.188–0.313 Aluminum			0.188–0.267 Aluminum			0.125 Aluminum up to 12' 0.188 Aluminum 14' and up			0.188 Aluminum		
HEIGHT/EPA WIND ZONE*	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH
	12'	16.91	9.82	12'	18.42	10.56	12'	12.81	7.47	12'	14.49	8.76
	14'	11.52	6.58	14'	12.51	7.03	14'	13.15	7.51	14'	9.07	5.20
	16'	9.45	5.08	16'	10.15	5.29	16'	10.78	5.79	16'	7.26	3.93
	18'	8.22	4.30	18'	8.78	4.43	18'	9.38	4.90			

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P5100 Series Poles, please visit www.hadco.com. Search by product name or number.



Shown: Pole: P8600. Fixture: TF9.



Ordering Guide

- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (I) Gray, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P8600 12 A**


PRODUCT CODE	P8600			BREAKAWAY BASE (OPTIONAL)		
TENON/TOP	6" O.D.					
(BASE TEMPLATE)						
BOLT CIRCLE	10" to 12" dia.			10" to 12.75" dia.		
ANCHOR RODS	(4) 3/4" dia. x 19" L			(4) 1" dia x 36" L		
BASE COVER	External Anchor Rods			Internal Anchor Rods		
SHAFT	6" Octagonal			—		
WALL	0.250-0.438			—		
HEIGHT/EPA WIND ZONE*	HT.	80 MPH	100 MPH	HT.	80 MPH	100 MPH
	12'	22.28	14.03			
	14'	19.11	11.96			
(with break-away base)	16'	16.50	10.25			

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P8000 Series Poles, please visit www.hadco.com. Search by product name or number.







Shown: Pole 9400, Fixture TWDCBH.



Ordering Guide


- Finishes: (A) Black, (B) White, (G) Verde, (H) Bronze, (J) Green
- Available in cast aluminum base with extruded aluminum shaft.

Ordering Example: **P9400 10 A**


PRODUCT CODE TENON/TOP	P9300 3" O.D.	P9400 3" O.D.	P9500 3" O.D.	P9600 3" O.D.
(BASE TEMPLATE)				
BOLT CIRCLE	7" dia.	8" to 9" dia.	8" to 9" dia.	9" to 10" dia.
ANCHOR RODS	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L	(4) 3/4" dia. x 19" L
BASE	9" dia.	9" square	9" square	10 1/4" square
BASE COVER	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods	Internal Anchor Rods
HAND -HOLE OPENING	2" x 4" Oval	2" x 4" Oval	2" x 4" Oval	2" x 4" Oval
SHAFT	4" Straight Flat Fluted	5" to 3" Tapered	5" Straight Flat Fluted	6" to 4" Tapered Fluted
WALL	0.188–0.313 Aluminum	0.125 Aluminum	0.188–0.267 Aluminum	0.125 Aluminum
HEIGHT/EPA WIND ZONE*	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH	HT. 80 MPH 100 MPH
	10' 16.65 10.15	10' 11.22 6.73	10' 24.87 15.71	12' 26.93 16.99
	12' 13.59 8.08	12' 9.03 5.23	12' 20.47 12.85	14' 18.22 11.44
	14' 8.97 5.16	14' 5.85 3.23	14' 13.68 8.51	16' 15.52 9.66
	16' 7.38 4.03	16' 4.67 2.37	16' 11.44 7.03	

*EPA values based on destructive break testing. For AASHTO ratings, contact factory.

For more information on P9000 Series Poles, please visit www.hadco.com. Search by product name or number.



Shown: Pole PSPT5019 polytech, Fixture: Custom.



Ordering Guide

Ordering Example: **PSPT3220 B M 25 A**

PRODUCT CODE	BASE TYPE*	LOADING		HEIGHT		FINISH
		(L) Low (.156" Wall Thickness)	(M) Medium (.188" Wall Thickness)	(12) 12'	(14) 14'	
	(B) Anchor Base			(16) 16'	(25) 25'	
	(D) Direct Bury	(H) High (.250" Wall Thickness)		(28) 28'	(30) 30'	(A) Black
PSPT3117	()	—		12, 14, 16		A
PSPT3220	B	()		25, 28, 30		A
PSPT5019	()	—		12, 14, 16		A

*Anchor Base (B) has aluminum structural pole with 10" – 12" bolt circle for 3/4" anchor rods.
NOTE: Direct Bury (D) has fiberglass structural pole..

For more information on the PSPT, please visit www.hadco.com. Search by product name or number.

Bases

Contents

SLB1791	47
SLB2200	47
SLBPT3117	47
SLBPT3220	48
SLBPT5019	48
WAB1150	49
WAB1716	49
WAB2100	49
WAB3200	49
WAB3300	50
WAB5000	50






Slipover Bases


SLB1791

- 10" Hex × 44" H (9 1/8" I.D.)
- 10 3/4" point to point
- 4" diameter poles
- One-piece
- 356 HM cast aluminum alloy




SLB2200

- 10 1/4" O.D. × 14" H (9 7/8" I.D.)
- 3" diameter poles
- One-piece
- 356 HM cast aluminum alloy




SLBPT3117

- 17" O.D. × 30 7/10" H
- 4", 5" and 6" diameter poles
- One-piece
- PolyTech™ custom blended polyethylene
- (A) Black only




SLBPT3220

- 20" O.D. x 35 7/10" H
- 6", 7" and 8" diameter poles
- One-piece
- PolyTech™ custom blended polyethylene
- (A) Black only



SLBPT5019

- 19" O.D. x 19" H
- 4", 5" and 6" diameter poles
- One-piece
- PolyTech™ custom blended polyethylene
- (A) Black only



Ordering Guide

Ordering Example: **SLB1791 4 A**


ACCESSORY	POLE DIAMETER		FINISH
	(3) 3"	(4) 4"	
	(5) 5"	(6) 6"	(A) Black
	(7) 7"	(8) 8"	(B) White
			(G) Verde
			(H) Bronze
			(J) Green
SLB1791	4		()
SLB2200	3		()
SLBPT3117	4, 5, 6		A
SLBPT3220	6, 7, 8		A
SLBPT5019	4, 5, 6		A

For more information on Slipover Bases, please visit www.hadco.com. Search by product name or number.

Wraparound Bases


WAB1150

- 11" O.D. × 29 3/4" H (10 5/8" I.D.)
- 3" and 4" diameter poles
- Two-piece
- 356 HM cast aluminum alloy




WAB2100

- 20" O.D. × 25" H (18 11/16" I.D.)
- 4", 5", 6" and 7" diameter poles
- Two-piece
- 356 HM cast aluminum alloy




WAB1716

- 16 1/4" corner to corner × 26 3/4" H (11 3/4" I.D.)
- 6", 7", and 8" diameter poles
- Two-piece octagon style
- 356 HM cast aluminum alloy



WAB3200


- 20" O.D. × 36" H (19 1/2" I.D.)
- 6" and 8" diameter poles
- Two-piece
- 356 HM cast aluminum alloy



Wraparound Bases


WAB3300

- 24" O.D. × 42 7/8" H (23 1/8" I.D.)
- 8" diameter poles
- Two-piece
- 356 HM cast aluminum alloy



WAB5000

- 17" O.D. × 19" H (16 1/2" I.D.)
- 5" diameter poles
- Two-piece
- 356 HM cast aluminum alloy



Ordering Guide

Ordering Example: **WAB1150 3 A**

ACCESSORY	POLE DIAMETER	POLE SHAPE (-) Round *(OCT) Octagonal	FINISH
	(3) 3" (4) 4" (5) 5" (6) 6" (7) 7" (8) 8"		(A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green
WAB1150	3, 4	-	()
WAB1716	6, 7, 8	()	()
WAB2100	4, 5, 6, 7	-	()
WAB3200	6, 8	-	()
WAB3300	8	-	()
WAB5000	5	-	()

*6" and 8" only in octagonal.

For more information on Wraparound Bases, please visit www.hadco.com. Search by product name or number.

Arms

Contents


HFP110	53
HFH2120	53
HFH2310	53
HFH2320	53
HFH2410	53
HFH2420	53
HFH2610	54
HGH2620	54
HFP110	55
HFP120	55
HFP210	55
HFP220	55
HFP310	56
HFP320	56
HFP410	56
HFP420	56
HFP510	56
HFP520	56
HFP 610	57
HFP620	57
HFP710	57
HFP720	57
HFP810	57
HFP820	57
HFP910	58
HFP1010	58
HFP1020	58
HFP1110	58
HFP1120	58
HFP1310	58
HFP1210	59
HFP1220	59
HFP1410	59
HFP1420	59
HFP2910	59
HFP2920	59
HFW190	60
HFW290	60
HFW390	60
HFW490	61
HFW2190	61
HFW2390	61
HFW2490	61
PTH2100	62
PTH2200	62
PTH2300	63
PTH2400	63
PTH2510	64
PTH2520	64
PTH2610	64
PTH2620	64
PTH2710	65
PTH2720	65
PTH2810	65
PTH2820	65
PTH2910	66
PTH2920	66
PTH3020	66
PTH3030	66
PTH3040	66
PTH3120	66
PTW085	67
PTW2180	67
PTW2280	68
PTW2285	68
PTW2380	68
PTW2480	69
PTW2580	69
PTW2780	69
PTW2880	70
PTW3080	70
PTW3180	70






Hanging Fixtures—Hub Mounting


HFH2110




HFH2120




HFH2310




HFH2320



HFH2410



HFH2420



Ordering Guide


Ordering Example: **HFH2410 P4 A**

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green			DESCRIPTION	EPA
HFH2110	P4	A, B, G, H, J			Single Arm	1.53
HFH2120	P4	A, B, G, H, J			Twin Arm (180°)	2.70
HFH2310	()	()			Single Arm	1.10
HFH2320	()	()			Twin Arm (180°)	1.70
HFH2410	P4	A, B, G, H, J			Single Arm	1.35
HFH2420	P4	A, B, G, H, J			Twin Arm (180°)	2.25


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Hub Mounting


HFH2610




HFH2620



HFH2910



HFH2920



Ordering Guide

Ordering Example: **HFH2910 P3 A**


PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	DESCRIPTION	EPA
HFH2610	P4*	A, B, G, H, J	Single Arm	1.90
HFH2620	P4*	A, B, G, H, J	Twin Arm (180°)	3.30
HFH2910	()	()	Single Arm	1.90
HFH2920	()	()	Twin Arm (180°)	3.30

*Recommended tenon size of 4" diameter x 6 1/2" length.


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Post Mounting


HFP110




HFP120



HFP210



HFP220



Ordering Guide


Ordering Example: **HFH2410 P4 A**

PRODUCT CODE	POST MOUNTING DIAMETER (P4) 4" Post Mounting	FINISH	ACCESSORY	POST MACHINING (PM)	DESCRIPTION	EPA
		(A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green				
HFP110	P4	()	N	PM	Single Arm	1.40
HFP120	P4	()	N	PM	Twin Arm (180°)	3.05
HFP210	P4	()	N	PM	Single Arm	2.30
HFP220	P4	()	N	PM	Twin Arm (180°)	3.65


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Post Mounting


HFP310




HFP320




HFP410




HFP420



HFP510



HFP520



Ordering Guide


Ordering Example: **HFP410 P4 H**

PRODUCT CODE	POST MOUNTING DIAMETER (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	ACCESSORY (F) Finial (R) Twistlock (N) None	POST MACHINING (PM)	DESCRIPTION	EPA
HFP310	P4	()	N	PM	Single Arm	3.05
HFP320	P4	()	N	PM	Twin Arm (180°)	5.70
HFP410	P4	()	N	—	Single Arm	1.05
HFP420	P4	()	N	—	Twin Arm (180°)	1.60
HFP510	P4	()	N	—	Single Arm	0.90
HFP520	P4	()	N	—	Twin Arm (180°)	1.90


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Post Mounting


HFP610




HFP620




HFP710




HFP720



HFP810



HFP820



Ordering Guide


Ordering Example: **HFP810 P4 B F**

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting (P5) 5" Post Mounting (P6) 6" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	ACCESSORY (F) Finial (R) Twistlock (N) None	POST MACHINING (PM)	DESCRIPTION	EPA
HFP610	P3, P4, P5	()	N	PM	Single Arm	1.10
HFP620	P3, P4, P5	()	N	PM	Twin Arm (180°)	2.05
HFP710	()	()	()	PM	Single Arm	3.00
HFP720	()	()	()	PM	Twin Arm (180°)	6.00
HFP810	()	A, B, G, H, J	()	PM	Single Arm	2.50
HFP820	()	A, B, G, H, J	()	PM	Twin Arm (180°)	5.00


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Post Mounting


HFP910




HFP1310




HFP1010




HFP1020



HFP1110



HFP1120



Ordering Guide

Ordering Example: **HFP1110 P4 A**


PRODUCT CODE	POST MOUNTING DIAMETER (P4) 4" Post Mounting (P5) 5" Post Mounting (P6) 6" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (J) Green	ACCESSORY (F) Finial (R) Twistlock (N) None	POST MACHINING (PM)	DESCRIPTION	EPA
HFP910	P3*	A	N	—	Single Arm	2.75
HFP1010	()	()	N	PM	Single Arm	2.50
HFP1020	()	()	N	PM	Twin Arm (180°)	5.00
HFP1110	()	()	()	PM	Single Arm	2.03
HFP1120	()	()	()	PM	Twin Arm (180°)	4.06
HFP1310	P4**	()	R, N	—	Single Arm	5.80

*A Tenon to be 3" O.D. x 9" Tall.
** Tenon to be 4.31" O.D. x 10" Tall.


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Post Mounting


HFP1210




HFP1220




HFP1410




HFP1420



HFP2910



HFP2920



Ordering Guide



Ordering Example: **HFP1410 P4 A**

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting (P5) 5" Post Mounting (P6) 6" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (J) Green	ACCESSORY (F) Finial (R) Twistlock (N) None	POST MACHINING (PM)	DESCRIPTION	EPA
HFP1210	P4, P5, P6	()	()	PM	Single Arm	1.53
HFP1220	P4, P5, P6	()	()	PM	Twin Arm (180°)	3.06
HFP1410	P4, P5, P6	()	()	PM	Single Arm	2.50
HFP1420	P4, P5, P6	()	()	PM	Twin Arm (180°)	5.00
HFP2910	P3, P4	()	N	—	Single Arm	1.90
HFP2920	P3, P4	()	N	—	Twin Arm (180°)	3.30



For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Wall Mounting



HFW190



HFW290



HFW390



Ordering Guide



Ordering Example: **HFW390 A**

PRODUCT CODE	FINISH	HEIGHT (J-box Center to Tenon Top)
	(A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	
HFW190	()	5 1/8"
HFW290	()	5 3/8"
HFW390	()	2 1/2"



For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Wall Mounting



HFW490





HFW2190



HFW2390



HFW2490



Ordering Guide


Ordering Example: **HFW2190 G**

PRODUCT CODE	FINISH	HEIGHT (J-box Center to Tenon Top)
	(A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	
HFW490	()	9 1/2"
HFW2190	A, B, G, H, J	2"
HFW2390	()	3 1/2"
HFW2490	A, B, G, H, J	4 3/4"



For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Hanging Fixtures—Hub Mounting



Configuration for Post-Top Fixtures • Hub Mounting are the same



PTH2100 Series w/3" Tenon



PTH2200 Series w/3" Tenon



Ordering Guide



Ordering Example: **PTH2110 P4 A**

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (J) Green	DESCRIPTION	EPA
PTH2110	()	()	1-Lite	1.53
PTH2120	()	()	2-Lite (180°)	2.70
PTH2140	()	()	4-Lite (90°)	3.57
PTH2150	()	()	5-Lite (90° & Center)	4.10
PTH2170	()	()	3-Lite (180° & Center)	3.10
PTH2210	()	()	1-Lite	0.85
PTH2220	()	()	2-Lite (180°)	1.35
PTH2240	()	()	4-Lite (90°)	1.95
PTH2250	()	()	5-Lite (90° & Center)	2.30
PTH2270	()	()	3-Lite (180° & Center)	1.62



For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Hub Mounting

PTH2300 Series w/3" Tenon



PTH2400 Series w/3" Tenon



Ordering Guide


Ordering Example: **PTH2340 P4 H**

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	DESCRIPTION	EPA
PTH2310	()	()	1-Lite	1.05
PTH2320	()	()	2-Lite (180°)	1.70
PTH2340	()	()	4-Lite (90°)	2.25
PTH2350	()	()	5-Lite (90° & Center)	2.59
PTH2370	()	()	3-Lite (180° & Center)	1.96
PTH2410	()	A, B, G, H, J	1-Lite	1.35
PTH2420	()	A, B, G, H, J	2-Lite (180°)	2.25
PTH2440	()	A, B, G, H, J	4-Lite (90°)	2.98
PTH2450	()	A, B, G, H, J	5-Lite (90° & Center)	3.27
PTH2470	()	A, B, G, H, J	3-Lite (180° & Center)	2.48


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Hub Mounting


PTH2510 w/3" Tenon




PTH2520 w/3" Tenon



PTH2610 w/3" Tenon



PTH2620 w/3" Tenon



Ordering Guide

Ordering Example: **PTH2510 P3 B**


PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (J) Green	DESCRIPTION	EPA
PTH2510	()	()	1-Lite	1.20
PTH2520	()	()	2-Lite (180°)	2.05
PTH2540	()	()	4-Lite (90°)	2.95
PTH2550	()	()	5-Lite (90° and center)	3.54
PTH2570	()	()	3-Lite (180° and center)	2.46
PTH2610	P4*	()	1-Lite	1.90
PTH2620	P4*	()	2-Lite (180°)	3.30

*Recommended tenon size of 4" diameter x 6 1/2" length.


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Hub Mounting


PTH2710 w/3" Tenon




PTH2720 w/3" Tenon



PTH2810 w/3" Tenon



PTH2820 w/3" Tenon



Ordering Guide


Ordering Example: **PTH2710 P3 B**

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	DESCRIPTION	EPA
PTH2710	()	A, B, G, H, J	1-Lite	1.40
PTH2720	()	A, B, G, H, J	2-Lite (180°)	2.30
PTH2740	()	A, B, G, H, J	4-Lite (90°)	3.01
PTH2750	()	A, B, G, H, J	5-Lite (90° and center)	3.55
PTH2770	()	A, B, G, H, J	3-Lite (180° and center)	2.63
PTH2810	()	()	1-Lite	0.95
PTH2820	()	()	2-Lite (180°)	1.45
PTH2840	()	()	4-Lite (90°)	2.05
PTH2850	()	()	5-Lite (90° and Center)	2.40
PTH2870	()	()	3-Lite (180° and Center)	1.70


For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Hub Mounting


PTH2910 w/3" Tenon




PTH2920 w/3" Tenon




PTH3020 Series w/2 3/8" or 3" Tenon




PTH3030 Series w/2 3/8" or 3" Tenon



PTH3040 Series w/2 3/8" or 3" Tenon



PTH3120 Series w/2 3/8" or 3" Tenon



Ordering Guide

Ordering Example: **PTH2910 P3 B**



PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FINISH (A) Black (B) White (G) Verde (H) Bronze (J) Green	DESCRIPTION	EPA
PTH2910	()	()	Single Arm	1.90
PTH2920	()	()	Twin Arm (180°)	3.30

PRODUCT CODE	POST MOUNTING DIAMETER (P3) 3" Post Mounting (P4) 4" Post Mounting	FIXTURE TENON (F2) 2 3/8" Tenon (F3) 3" Tenon	FINISH (A) Black (B) White (G) Verde (H) Bronze (J) Green	DESCRIPTION	EPA
PTH3020	()	()	()	2-Lite (180°)	1.31
PTH3030	()	()	()	3-Lite (120°)	1.35
PTH3040	()	()	()	4-Lite (90°)	1.38
PTH3120	()	()	()	2-Lite (180°)	1.00



For more information on Arm Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Wall Mounting

PTW085 w/3" Tenon



PTW2180 w/3" Tenon



Ordering Guide

Ordering Example: **PTW085 G**



PRODUCT CODE	FINISH	HEIGHT (J-box Center to Tenon Top)
	(A) Black (B) White (G) Verde (H) Bronze (J) Green	
PTW085*	()	4 3/4"
PTW2180	()	6 3/4"

*Note: Can only be used with fixtures 22" diameter or less.



For more information on Wall Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Wall Mounting



PTW2280 w/3" Tenon



PTW2285 w/3" Tenon



PTW2380 w/3" Tenon



Ordering Guide



Ordering Example: **PTW2280 A**

PRODUCT CODE	FINISH	HEIGHT (J-box Center to Tenon Top)
	(A) Black (B) White (G) Verde (H) Bronze (I) Gray (J) Green	
PTW2280	A, B, G, H, J	3 7/8"
PTW2285	A, B, G, H, J	3 7/8"
PTW2380	()	11"



For more information on Wall Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures—Wall Mounting



PTW2480 w/3" Tenon



PTW2580 w/3" Tenon



PTW2780 w/3" Tenon



Ordering Guide



Ordering Example: **PTW2480 J**

PRODUCT CODE	FINISH	HEIGHT (J-box Center to Hanger Bottom)
	(A) Black (B) White (G) Verde (H) Bronze (J) Green	
PTW2480	()	12 3/4"
PTW2580	()	9 3/4"
PTW2780	()	4 1/4"



For more information on Wall Brackets, please visit www.hadco.com. Search by product name or number.

Post-Top Fixtures–Wall Mounting



PTW2880 w/3" Tenon



PTW3080 w/2 3/8" or 3" Tenon



PTW3180 w/2 3/8" or 3" Tenon



Ordering Guide

Ordering Example: **PTW2880 J**

PRODUCT CODE	FINISH		HEIGHT (J-box Center to Hanger Bottom)
	(A) Black	(H) Bronze	
	(B) White	(I) Gray	
	(G) Verde	(J) Green	
PTW2880	()		7 1/4"

PRODUCT CODE	FIXTURE TENON (F2) 2 3/8" Tenon (F3) 3" Tenon	FINISH		HEIGHT (J-box Center to Hanger Bottom)
		(A) Black	(H) Bronze	
		(B) White	(I) Gray	
		(G) Verde	(J) Green	
PTW3080	()	()	()	7"
PTW3180	()	()	()	7 1/2"

For more information on Wall Brackets, please visit www.hadco.com. Search by product name or number.

Accessories

Contents

Photocells	73
Receptacles	73
Ladder Rest	73
Pier Base	74
Post Adaptors	74
BA Banner Arm Bracket	75
FHB Flag Holder Bracket	75
FPB Flower Pot Bracket	76
TD Tie Down Bracket	76





Pole Accessories

Specifications

These accessories are engineered to work seamlessly with Hadco installations – so you can complete the job efficiently, with safety and confidence.

Photocells

M0004

- Button eye photocell
- 120V



M0005


- Button eye photocell
- 208V or 277V



Receptacles

M0006

- Single weatherproof outlet receptacle for round post



M0007

- Single weatherproof outlet receptacle for flat surface mounting



Ladder Rest

M0012

- Ladder rest
- Fits 3" O.D. posts
- Extended 3" tenon
- 356 HM cast aluminum alloy



Pier Base

M0080

- Single pier base
- 9 1/2" diameter
- 3" O.D. tenon
- 7" bolt circle
- 356 HM cast aluminum and extruded aluminum



Post Adaptors

M0090

- Post adaptor
- 4" O.D. post fitter
- 3" O.D. fixture tenon
- 356 HM cast aluminum alloy



Ordering Guide


Ordering Example: **SLB1500 3 A**

		FINISH
		(A) Black
		(B) White
		(G) Verde
		(H) Bronze
		(J) Green
ACCESSORY		
M0004		N/A
M0005		N/A
M0006	()	
M0007	()	
M00012	()	
M00080	()	
M00090	()	


For more information on Accessories, please visit www.hadco.com. Search by product name or number.

Banner Arms, Holders and Brackets

BA Banner Arm Bracket



FHB Flag Holder Bracket



Ordering Guide

Ordering Example: **BA 32 A 24 B A**


ACCESSORY	POST DIAMETER		# OF ARMS	ALUMINUM	ARM LENGTH		BALL	FLAG POLE DIAMETER	FINISH
	(3) 3"	(4) 4"			(12) 12"	(18) 18"			
	(5) 5"		(1) One	(A)	(24) 24"	(30) 30"	(B)	(1" Standard)	(A) Black
BA*	3, 4, 5		(2) Two at 180°	A	18, 24, 30		B	—	(B) White
FHB	4, 5			—	—		—	1	(G) Verde
									(H) Bronze
									(J) Green

*Note: Consult factory for maximum banner size.


For more information on Accessories, please visit www.hadco.com. Search by product name or number.

Banner Arms, Holders and Brackets

FPB Flower Pot Bracket



TD Tie Down Bracket



Ordering Guide

Ordering Example: **TD 3 1 A**

ACCESSORY	POST DIAMETER	# OF ARMS	ARM LENGTH	FINISH
				(A) Black (B) White (G) Verde (H) Bronze (J) Green
FPB	4, 5	()	12	()
TD	3, 4, 5	()	—	()

For more information on Accessories, please visit www.hadco.com. Search by product name or number.

Photo Gallery

The following images illustrate the function and versatility of Philips Hadco's lighting fixtures, arms and poles while adding character to your environment's setting.



Philips Hadco LED roadway luminaires provide crisp, brilliant white light making roadways, vehicular and pedestrian traffic, and surrounding areas appear brighter and more vibrant. Driver and pedestrian visibility is enhanced for safer roadways.



The RX3 is a perfect example of how we harmonize form and function to provide optimum lighting performance with a sleek design. Our LED roadway luminaires complement every type of roadway and surrounding architecture.



RX1 and RX2 luminaires are the ideal cobrahead replacement. Very low profile that maintains the cobrahead "look" from the ground-up means our LED luminaires virtually disappear while providing dynamic LED lighting.



In addition to roadways, other applications including car lots benefit from our solutions. Colors are more dramatic and "pop" under LED lighting, which heightens visual interest contributing to increased customer traffic and sales.



Precise optics of Philips Hadco's Refractive Globes - coupled with a range of styles and options like banner arms and customizable street graphics, offer an attractive presence both day and night.



Philips Hadco Teardrop fixtures offer an alternative to the cobrahead traditionally used to light high traffic locations, while adding character:



© 2012 Philips Group

All rights reserved. Certain products illustrated in this catalog may be protected by applicable patents and patent pending. Philips Hadco will aggressively defend all of its intellectual property. We reserve the right to change details of design, materials and finishes in any way that will not alter installed appearance or reduce function and performance.



PHILIPS
HADCO

www.hadco.com

100 Craftway Drive, P.O. Box 128, Littlestown, PA 17340

Phone: 1-800-331-4185 • Fax: 717-359-9289

Printed in U.S.A. PH-1080-1209-3K