

PHILIPS Proflood LED BCP608

220V
240V

outdoor

CE

IEC
EN60598

IP66

max
+35°C



min
-20°C

Ta
Max.
25°C







0.1m

	led color	LEDs	W +/-10%			kg	m²
BCP608 EB GOBO GR10714	740	LED55	55	✓	✓	18.2	0.12
BCP608 EB SHUTTERS GR10714	740	LED55	55	✓	✓	18.2	0.12
BCP608 EB GOBO + SHUTTERS GR10714	740	LED55	55	✓	✓	18.2	0.12
BCP608 EB GOBO RAL.	740	LED55	55	✓	✓	18.2	0.12
BCP608 EB SHUTTERS RAL.	740	LED55	55	✓	✓	18.2	0.12
BCP608 EB GOBO + SHUTTERS RAL.	740	LED55	55	✓	✓	18.2	0.12


	GOBO	SHUTTERS	GOBO + SHUTTERS
GOBO A	✓		✓
GOBO B	Whith adaptator		Whith adaptator
Colour filter F-RD/F-BL/F-GN/F-YE	✓	✓	✓




i




1a









1b






2











© 2016 Koninklijke Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent – or other industrial or intellectual property rights.

Philips Lighting B.V.
The Netherlands