


PHILIPS ADVANCE

Electrical Specifications

G-2S110-TP	
Brand Name	MARK III
Ballast Type	Magnetic
Starting Method	Rapid Start
Lamp Connection	Series
Input Voltage	347
Input Frequency	60 HZ
Status	Active

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/°C)	Input Current (Amps)	Input Power (Watts)	Ballast Factor	MAX THD %	Power Factor	Lamp Current Crest Factor	B.E.F.
* F72T12/HO	2	85	-20/-29	0.57	193	0.94	20	0.96	1.8	0.49
F96T12/HO	2	110	-20/-29	0.69	237	0.95	20	0.98	1.7	0.40
F96T12/HO/ES	2	95	60/16	0.61	201	0.90	20	0.96	1.8	0.45

Wiring Diagram




Diag. 21

The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

	in.	cm.		in.	cm.
Black	22	55.9	Yellow/Blue		0
White	22	55.9	Blue/White		0
Blue	46	116.8	Brown		0
Red	46	116.8	Orange		0
Yellow	70	177.8	Orange/Black		0
Gray		0	Black/White		0
Violet		0	Red/White		0

Enclosure



Enclosure Dimensions

OverAll (L)	Width (W)	Height (H)	Mounting (M)
11.75 "	3.1875 "	2.625 "	11.14062 "
11 3/4	3 3/16	2 5/8	11 9/64
29.8 cm	8.1 cm	6.7 cm	28.3 cm



Revised 09/10/99

Data is based upon tests performed by Philips Lighting N.A in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

Philips Lighting Electronic N.A

10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882
Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886