


Greenperform Waterproof /防水LED支架灯


WT160C/WT161C

Mounting instruction/安装说明

4441 000 78801



Type Desc 型号描述	Power(W) 灯具功率	Vol. / Fre. 电压/频率	Dim.(W×H×L) (mm) 灯具尺寸(宽×高×长)	CCT 色温	kg
WT160C/LED10/L60	12	220-240~ 50/60Hz	74×58×635	CW(冷白光)/NW(正白光)	0.7
WT160C/LED20/L60	20		74×58×635		0.7
WT160C/LED20/L120	20		74×58×1197		1.2
WT160C/LED40/L120	40		74×58×1197		1.3
WT160C/LED50/L150	55		74×58×1478		1.7
WT161C/LED10/L60	12		74×58×666		0.7
WT161C/LED20/L60	20		74×58×666		0.7
WT161C/LED20/L120	20		74×58×1228		1.3
WT161C/LED40/L120	40		74×58×1228		1.4
WT161C/LED50/L150	55		74×58×1509		1.8
WT160C/LED20/L60/AM	20		74×58×635	AM(黄光)	0.7
WT160C/LED40/L120/AM	40		74×58×1197		1.3
WT161C/LED20/L60/AM	20		74×58×666		0.7
WT161C/LED40/L120/AM	40		74×58×1228		1.4



Accessories for Optiona / 可选附件

Type Desc 型号描述	Accessories Desc 附件名称
WT161Z TB	连接线



- 1、The luminaire shall be installed by a qualified electrician and wired in a ccordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装，接线要符合IEE电气标准或国家标准。
- 2、Do not switch on before complete installation.
接线过程中，切勿通电。
- 3、The luminaire shall under no circumstance, be covered with insulation matting or similar material.
灯具不适合被隔热衬垫或类似材料覆盖。
- 4、The luminaire is suitable for direct mounting on normally flammable material.
灯具适合于直接安装在普通可燃材料表面。
- 5、Don't apply to high corrosive gas situation.
本灯具不适用于高腐蚀性气体的场合。

