



TCS050

TCS050 2xTL-D32W/840 EB C5

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, High-gloss optic double parabolic

The TCS050 luminaires have been specially developed for indoor commercial lighting. They are available in recessed (TBS050) and surface-mounted (TCS050) models. This is an economical modular range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TCS offers the option of two optical systems that enable design freedom in projects, energy savings, excellent lighting efficiency, and easy installation.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TCS050 2xTL-D32W/840 EB C5
Full product name	TCS050 2xTL-D32W/840 EB C5
Full product code	820619252931
Order code	820619252931
Material Nr. (12NC)	820619252931
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

TCS050

Dimensional drawing

Dimensões em mm:

Sobrepor (TCS 050)

