



TCS050

TCS050 2xTL-D32W/840 EB C1

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, High-gloss mirror flat lamellae louver

The TCS050 luminaires have been specially developed for indoor commercial lighting. They are available in recessed (TBS050) and surface-mounted (TCS050) models. This is an economical modular range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TCS offers the option of two optical systems that enable design freedom in projects, energy savings, excellent lighting efficiency, and easy installation.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss mirror flat lamellae louver
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TCS050 2xTL-D32W/840 EB C1
Full product name	TCS050 2xTL-D32W/840 EB C1
Full product code	820619253091
Order code	820619253091
Material Nr. (12NC)	820619253091
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

TCS050

Dimensional drawing

Dimensões em mm:

Sobrepor (TCS 050)

