



# TBS050 A

## TBS050 4xTL-D16W/840 EB C5

4, MASTER TL-D, 16 W, 840 neutral white, Electronic, High-gloss optic double parabolic

The TBS050 luminaires were specially developed for interior commercial lighting, and are available in recessed (TBS050) and surface-mounted (TCS050) models. This is an economical modular range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TBS can be recessed in any type of ceiling (plaster or paneled) and offers the option of two optical systems that offer design freedom in projects, energy savings, excellent lighting efficiency, and easy installation.

### Product data

| General Information      |                                   |
|--------------------------|-----------------------------------|
| Lamp family code         | TL-D [MASTER TL-D]                |
| Gear                     | EB [Electronic]                   |
| Light Technical          |                                   |
| Number of light sources  | 4                                 |
| Light source color       | 840 neutral white                 |
| Optic type               | High-gloss optic double parabolic |
| Operating and Electrical |                                   |
| Power Consumption        | 16 W                              |

| Product Data                    |                            |
|---------------------------------|----------------------------|
| Order product name              | TBS050 4xTL-D16W/840 EB C5 |
| Full product name               | TBS050 4xTL-D16W/840 EB C5 |
| Full product code               | 820619253361               |
| Order code                      | 820619253361               |
| Material Nr. (12NC)             | 820619253361               |
| Numerator - Quantity Per Pack   | 1                          |
| Numerator - Packs per outer box | 1                          |

TBS050 A

Dimensional drawing

Dimensões em mm:

Embutir (TBS 050)

