



MDK500

GDK500 P-AC LENTE PRISMATICO

Acrylic cover prismatic

The MDK luminaire is ideal for use in large indoor areas and provides three-dimensional lighting with an excellent level of illumination in the vertical and horizontal planes. The acrylic diffuser creates an environment free of glare and shadows, ensuring greater visual comfort. It includes a housing for ancillary equipment, and a clear acrylic diffuser for 250 or 400 W metal-halide and sodium vapor lamps. It has a hook for support and an aluminum box for heat dissipation.

Product data

Product Data	
Order product name	GDK500 P-AC LENTE PRISMATICO
Full product name	GDK500 P-AC LENTE PRISMATICO
Full product code	820619254531
Order code	820619254531
Material Nr. (12NC)	820619254531

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001605
Numerator - Packs per outer box	10
EAN/UPC - Case	7894400001605