



Megalux TCS912

TCS912 2xTL-D32W/840 EB C5

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, High-gloss optic double parabolic

Featuring an elegant, compact design, Megalux luminaires are specially designed for use with TL-D tubular fluorescent lamps of 16 or 32 W. Ideal for indoor use such as in offices or commercial areas. Available in recessed and surface-mounted versions, they can be recessed in any type of ceiling (plaster or paneled). Two optic options provide the freedom to create projects that are fully integrated into the environment while also providing efficient and economical lighting. They are easy to install and the ballast is accessed from below without the need to remove the luminaire from the installed location.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TCS912 2xTL-D32W/840 EB C5
Full product name	TCS912 2xTL-D32W/840 EB C5
Full product code	820619255441
Order code	820619255441
Material Nr. (12NC)	820619255441
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Megalux TCS912

Dimensional drawing

Dimensões em mm:

TCS 912

