



SlimLine TBS020

TBS020 A 2XTLD16W/840 EB C5

2, MASTER TL-D, 16 W, 840 neutral white, Electronic, High-gloss optic double parabolic

SlimLine luminaires are compact and versatile for better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic
Optical cover type	-
Operating and Electrical	
Power Consumption	16 W

Product Data	
Order product name	TBS020 A 2XTLD16W/840 EB C5
Full product name	TBS020 A 2XTLD16W/840 EB C5
Full product code	820619256139
Order code	820619256139
Material Nr. (12NC)	820619256139
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

SlimLine TBS020

Dimensional drawing

Dimensões em mm:

Embutir (TBS 020)

