



# Megalux TBS912

## TBS912 4xTL-D16W/840 EB C1

4, MASTER TL-D, 16 W, 840 neutral white, Electronic, High-gloss mirror flat lamellae louver

Featuring an elegant, compact design, Megalux luminaires are specially designed for use with TL-D tubular fluorescent lamps of 16 or 32 W. Ideal for indoor use such as in offices or commercial areas. Available in recessed and surface-mounted versions, they can be recessed in any type of ceiling (plaster or paneled). Two optic options provide the freedom to create projects that are fully integrated into the environment while also providing efficient and economical lighting. They are easy to install and the ballast is accessed from below without the need to remove the luminaire from the installed location.

### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss mirror flat lamellae louver
Operating and Electrical	
Power Consumption	16 W

Product Data	
Order product name	TBS912 4xTL-D16W/840 EB C1
Full product name	TBS912 4xTL-D16W/840 EB C1
Full product code	820619257061
Order code	820619257061
Material Nr. (12NC)	820619257061
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Megalux TBS912

### Dimensional drawing

#### Dimensões em mm:

TBS 912

