



# Pacific TCW216

## ZTX400 MB-WAPR (2PCS)

TTX400 ACC.

Functional shock-, vandal-, dust-, and jetproof luminaire for TL-D and TL5 fluorescent lamps. Fibre-glass reinforced polyester housing with a polycarbonate prismatic clear cover. Fixation of the cover to the housing without additional lockers, but by innovative concept with integrated fixation points. Gear tray, 2 stainless steel ceiling fixation clips and cable entries (membranes) supplied with the luminaire. Choice of different standard versions available: versions 1/2 x 18W, 1/2 x 36W, 1/2 x 58W (TL-D) and 1/2 x 49W (TL5), emergency lighting, 1- or 3 hours, ready-to-install, including lamp(s) and Waterproof External Connector (WEC), equipped with through-wiring 5 x 2.5 mm².

### Product data

General Information			
Product family code	ZTX400 [TTX400 ACC.]	Material Nr. (12NC)	910400647118
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559094434
		Numerator - Packs per outer box	20
		EAN/UPC - Case	8711559094441
Product Data			
Order product name	ZTX400 MB-WAPR (2PCS)		
Full product name	ZTX400 MB-WAPR (2PCS)		
Full product code	871155909443499		
Order code	09443499		