



Mini 300 Cube DBP300

ZBP300 IP WH

IP WH, White

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Product data

| General Information | | | |
|---------------------|-----------------|---------------------------------|---------------|
| Accessory color | White | Order code | 910400793201 |
| Product family code | ZBP300 [IP WH] | Material Nr. (12NC) | 910400793201 |
| | | Numerator - Quantity Per Pack | 1 |
| | | EAN/UPC - Product/Case | 8690653181298 |
| | | Numerator - Packs per outer box | 1 |
| | | EAN/UPC - Case | 8690653181298 |
| Product Data | | | |
| Order product name | ZBP300 IP WH | | |
| Full product name | ZBP300 IP WH | | |
| Full product code | 869065318129800 | | |