



SmartForm TBS460

ZBS600 C3000W3

SmartForm TBS460, Accessory

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in square and rectangular versions. Designed to fit in a wide range of ceiling types, SmartForm can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS460 – ultra-flat 'light beam'. SmartForm recessed TBS460 'light beam' luminaires are built around superior micro-optics and have a build-in height of a mere 45 mm, making them ideal for applications requiring very flat light fittings, e.g. refurbishment projects where ceiling space may be especially limited.

Product data

| General Information | | Material Nr. (12NC) | |
|---------------------|-----------------|---------------------------------|---------------|
| Product family code | ZBS600 [ZBS600] | Numerator - Quantity Per Pack | 1 |
| Product Data | | EAN/UPC - Product/Case | 8711559597744 |
| Order product name | ZBS600 C3000W3 | Numerator - Packs per outer box | 25 |
| Full product name | ZBS600 C3000W3 | EAN/UPC - Case | 8711559597751 |
| Full product code | 871155959774499 | | |
| Order code | 910400898803 | | |