



# T8 e-batten TMS150

GMS150 2 18 P

2, 18 W

The new range of Philips fluorescent electronic ballasts are lightweight and easy to install thanks to their new cover plate. They're energy-efficient too, providing the perfect solution for virtually any commercial environment. The TMS150 range comes in the usual T8 models. Or you can choose the new TMS151 T5 models for even greater energy savings – up to 20% over standard T8 electronic ballasts. The new, high-quality European HFP111 programmed-start ballasts ensure superior performance and extended lamp life. The new e-battens can be adapted to a variety of environments using an extensive range of optional attachments that include prismatic diffusers, industrial reflectors and wire guards. Emergency and dimming options are available upon request.

## Product data

<b>Light Technical</b>	
Number of light sources	2
<b>Operating and Electrical</b>	
Power Consumption	18 W
<b>Product Data</b>	
Order product name	GMS150 2 18 P
Full product name	GMS150 2 18 P

Full product code	871155954522601
Order code	910400966891
Material Nr. (12NC)	910400966891
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559545226
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559545233