



# T8 e-batten TMS150

TMS151 1xTL5-28W HF-P F 220-240V 50/60Hz

1, TL5, 28 W, HF Performer, 220 to 240 V, 50 to 60 Hz

The new range of Philips fluorescent electronic ballasts are lightweight and easy to install thanks to their new cover plate. They're energy-efficient too, providing the perfect solution for virtually any commercial environment. The TMS150 range comes in the usual T8 models. Or you can choose the new TMS151 T5 models for even greater energy savings – up to 20% over standard T8 electronic ballasts. The new, high-quality European HFP111 programmed-start ballasts ensure superior performance and extended lamp life. The new e-battens can be adapted to a variety of environments using an extensive range of optional attachments that include prismatic diffusers, industrial reflectors and wire guards. Emergency and dimming options are available upon request.

## Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
CE mark	Yes
Light Technical	
Number of light sources	1
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	28 W

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMS151 1xTL5-28W HF-P F 220-240V 50/60Hz
Full product name	TMS151 1xTL5-28W HF-P F 220-240V 50/60Hz
Full product code	910400966901
Order code	910400966901
Material Nr. (12NC)	910400966901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559545417
Numerator - Packs per outer box	6

## T8 e-batten TMS150

### Dimensional drawing

