



# T8 e-batten TMS150

**TMS151 2xTL5-35W HF-P F P 220-240V 50/60**

2, TL5, 35 W, HF Performer, 220 to 240 V, 50 to 60 Hz, Acrylic cover prismatic

The new range of Philips fluorescent electronic ballasts are lightweight and easy to install thanks to their new cover plate. They're energy-efficient too, providing the perfect solution for virtually any commercial environment. The TMS150 range comes in the usual T8 models. Or you can choose the new TMS151 T5 models for even greater energy savings – up to 20% over standard T8 electronic ballasts. The new, high-quality European HFP111 programmed-start ballasts ensure superior performance and extended lamp life. The new e-battens can be adapted to a variety of environments using an extensive range of optional attachments that include prismatic diffusers, industrial reflectors and wire guards. Emergency and dimming options are available upon request.

## Product data

<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	TL5 [TL5]	35 W	
Gear	HFP [HF Performer]	<b>Application Conditions</b>	
CE mark	Yes	Suitable for random switching	
<b>Light Technical</b>		<b>Product Data</b>	
Number of light sources	2	Order product name	TMS151 2xTL5-35W HF-P F P 220-240V 50/60
Optical cover type	Acrylic cover prismatic	Full product name	TMS151 2xTL5-35W HF-P F P 220-240V 50/60
<b>Operating and Electrical</b>		Full product code	910400966904
Input Voltage	220 to 240 V	Order code	910400966904
Line Frequency	50 to 60 Hz	Material Nr. (12NC)	910400966904
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559545448

T8 e-batten TMS150

Numerator - Packs per outer box	1
---------------------------------	---

Dimensional drawing

