



Halolite

QVF135 HAL-TDS500W K BK CN

Plusline Small (double-ended), 500 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

Product data

General Information	
Lamp family code	HAL-TDS [Plusline Small (double-ended)]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	500 W
Mechanical and Housing	
Housing Color	Black

Product Data	
Order product name	QVF135 HAL-TDS500W K BK CN
Full product name	QVF135 HAL-TDS500W K BK CN
Full product code	910401266580
Order code	910401266580
Material Nr. (12NC)	910401266580
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687328
Numerator - Packs per outer box	12

Dimensional drawing

