

# TBH375

## TBH375 3xTL-D58W HFP

TBH375, 3, MASTER TL-D, 58 W, HF Performer

Ball-impact-resistant luminaire for TL-D fluorescent lamps, specially designed for multipurpose sports halls and tennis halls. Lamellae prevent players from seeing directly into the lamps. Strong housing construction protects lamps against ball impact. For surface or recessed mounting. Optics supplied with the luminaire.


### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFP [HF Performer]
Product family code	TBH375 [TBH375]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	3
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	58 W
Connection	Push-in connector 3-pole
Mechanical and Housing	
Overall width	463 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBH375 3xTL-D58W HFP
Full product name	TBH375 3xTL-D58W HFP
Full product code	871155905096600
Order code	910401529303
Material Nr. (12NC)	910401529303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559050966
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559050966

TBH375

Dimensional drawing



Product
TBH375 3xTL-D58W HFP

