



Halolite

QVF135 HAL-TDS500W 220V-50Hz

Plusline Small (double-ended), 500 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

Product data

| General Information | |
|--------------------------|---|
| Lamp family code | HAL-TDS [Plusline Small (double-ended)] |
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Power Consumption | 500 W |
| Product Data | |
| Order product name | QVF135 HAL-TDS500W 220V-50Hz |

| | |
|---------------------------------|------------------------------|
| Full product name | QVF135 HAL-TDS500W 220V-50Hz |
| Full product code | 910401631280 |
| Order code | 910401631280 |
| Material Nr. (12NC) | 910401631280 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163289175 |
| Numerator - Packs per outer box | 12 |

Dimensional drawing

