



# MVF607 C New Decoflood

MVF607 CSON-T150W K 220V-50Hz NB

SON-T, 150 W, Narrow beam

A large, high-grade rotational symmetrical floodlight for SON-T Plus and metal halide lamps. It is suitable for city environments. Its all-weather construction is designed for simple cleaning and speedy servicing.

## Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optic type outdoor	Narrow beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	150 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MVF607 CSON-T150W K 220V-50Hz NB
Full product name	MVF607 CSON-T150W K 220V-50Hz NB
Full product code	910401635380
Order code	910401635380
Material Nr. (12NC)	910401635380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## MVF607 C New Decoflood

### Dimensional drawing

