



# MVF607 C New Decoflood

## MVF607 CHPI-TP400W K 220V-50Hz NB

MASTER HPI-T Plus, 400 W, Narrow beam

A large, high-grade rotational symmetrical floodlight for SON-T Plus and metal halide lamps. It is suitable for city environments. Its all-weather construction is designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Gear	HGR [HPL/HPI gear]

  

Light Technical	
Number of light sources	1
Optic type outdoor	Narrow beam

  

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	400 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

  

Product Data	
Order product name	MVF607 CHPI-TP400W K 220V-50Hz NB
Full product name	MVF607 CHPI-TP400W K 220V-50Hz NB
Full product code	910401635680
Order code	910401635680
Material Nr. (12NC)	910401635680
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# MVF607 C New Decoflood

## Dimensional drawing

