



# MVF616 C New Decoflood

## MVF616 CMHN-TD150W K 220V-50Hz WB

MHN-TD, 150 W, Wide beam

A medium-sized, high-grade floodlight with a choice of light distributions from a variety of lamps. It is well suited to city environments. Its all-weather construction is designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	MHN-TD
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	150 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Product Data	
Order product name	MVF616 CMHN-TD150W K 220V-50Hz WB
Full product name	MVF616 CMHN-TD150W K 220V-50Hz WB
Full product code	910401636580
Order code	910401636580
Material Nr. (12NC)	910401636580
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291993346
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291993346

## MVF616 C New Decoflood

### Dimensional drawing

