



# Landmark MVF028

## MVF028 MHN-LA1000W 220-240V MB

MASTER MHN-LA, 1000 W, Medium beam

A high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact unit distributes a well-controlled, low glare, wide, medium or narrow beam evenly, accurately and efficiently. Excellent lighting results are achieved with the double-ended 2000W metal-halide lamp and also with standard 1000W metal-halide or high-pressure sodium lamps. Rugged all-weather construction designed for easy aiming, simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Gear	CONV [Conventional]

  

Light Technical	
Number of light sources	1
Optic type outdoor	Medium beam

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Power Consumption	1,000 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

  

Product Data	
Order product name	MVF028 MHN-LA1000W 220-240V MB
Full product name	MVF028 MHN-LA1000W 220-240V MB
Full product code	910401639580
Order code	910401639580
Material Nr. (12NC)	910401639580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Landmark MVF028

## Dimensional drawing

