



Landmark MVF028

MVF028 MHN-LA1000W 220-240V MB

MASTER MHN-LA, 1000 W, Medium beam

A high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact unit distributes a well-controlled, low glare, wide, medium or narrow beam evenly, accurately and efficiently. Excellent lighting results are achieved with the double-ended 2000W metal-halide lamp and also with standard 1000W metal-halide or high-pressure sodium lamps. Rugged all-weather construction designed for easy aiming, simple cleaning and speedy servicing.

Product data

| General Information | |
|--------------------------|------------------------|
| Lamp family code | MHN-LA [MASTER MHN-LA] |
| Gear | CONV [Conventional] |
| Light Technical | |
| Number of light sources | 1 |
| Optic type outdoor | Medium beam |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 Hz |
| Power Consumption | 1,000 W |

| Approval and Application | |
|---------------------------------|--|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Product Data | |
| Order product name | MVF028 MHN-LA1000W 220-240V MB |
| Full product name | MVF028 MHN-LA1000W 220-240V MB |
| Full product code | 910401639580 |
| Order code | 910401639580 |
| Material Nr. (12NC) | 910401639580 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Landmark MVF028

Dimensional drawing

