



# ZVF350

## ZVF350 SON-T1000W 230V-50Hz

SON-T, 1000 W

This is a range of pre-wired, high-pressure die-casted aluminum gear boxes. It is available for high wattage lamps, ranging from SON-T/HPI-T 10000W to MHN-SA 2000W. These gear boxes are normally used in combination with floodlights which are not able to integrate with electrical components due to lack of space or high temperatures.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Power Consumption	1,000 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Product Data	
Order product name	ZVF350 SON-T1000W 230V-50Hz
Full product name	ZVF350 SON-T1000W 230V-50Hz
Full product code	910401642080
Order code	910401642080
Material Nr. (12NC)	910401642080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291993407
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291993407

ZVF350

Dimensional drawing

