



# Halolite

## QVF133 HAL-TDS150W K BK NZ

Plusline Small (double-ended), 150 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

### Product data

General Information	
Lamp family code	HAL-TDS [Plusline Small (double-ended)]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	150 W
Mechanical and Housing	
Housing Color	Black

Product Data	
Order product name	QVF133 HAL-TDS150W K BK NZ
Full product name	QVF133 HAL-TDS150W K BK NZ
Full product code	910401643380
Order code	910401643380
Material Nr. (12NC)	910401643380
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163289199
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163289243

Dimensional drawing

