



# Halolite

## QVF135 HAL-TDS500W K BK NZ

Plusline Small (double-ended), 500 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

### Product data

| General Information      |   |
|--------------------------|---|
| Lamp family code         | HAL-TDS [Plusline Small (double-ended)] |
| Light Technical          |   |
| Number of light sources  | 1                                       |
| Operating and Electrical |   |
| Input Voltage            | 240 V                                   |
| Line Frequency           | 50 Hz                                   |
| Power Consumption        | 500 W                                   |
| Mechanical and Housing   |   |
| Housing Color            | Black                                   |

| Product Data                    |                            |
|---------------------------------|----------------------------|
| Order product name              | QVF135 HAL-TDS500W K BK NZ |
| Full product name               | QVF135 HAL-TDS500W K BK NZ |
| Full product code               | 910401643480               |
| Order code                      | 910401643480               |
| Material Nr. (12NC)             | 910401643480               |
| Numerator - Quantity Per Pack   | 1                          |
| EAN/UPC - Product/Case          | 8710163289205              |
| Numerator - Packs per outer box | 12                         |
| EAN/UPC - Case                  | 8710163289250              |

## Dimensional drawing

