



Optivision MVP507 C

MVP507 CSON-T600W 220-240V WB

SON-T, 600 W, Wide beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Light source color	-
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Power Consumption	600 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MVP507 CSON-T600W 220-240V WB
Full product name	MVP507 CSON-T600W 220-240V WB
Full product code	910401647580
Order code	910401647580
Material Nr. (12NC)	910401647580
Local order code	910401647580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Optivision MVP507 C

Dimensional drawing

