



Optivision MVP507 C

MVP507 CMHN-LA1000W 220-240V WB

MASTER MHN-LA, 1000 W, Wide beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

Product data

General Information		Approval and Application	
Lamp family code	MHN-LA [MASTER MHN-LA]	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Gear	CONV [Conventional]		
Light Technical		Product Data	
Number of light sources	1	Order product name	MVP507 CMHN-LA1000W 220-240V WB
Light source color	-	Full product name	MVP507 CMHN-LA1000W 220-240V WB
Optic type outdoor	Wide beam	Full product code	910401647780
		Order code	910401647780
		Material Nr. (12NC)	910401647780
Operating and Electrical		Numerator - Quantity Per Pack	1
Input Voltage	220 to 240 V	Numerator - Packs per outer box	1
Line Frequency	50 Hz		
Power Consumption	1,000 W		

Optivision MVP507 C

Dimensional drawing

