



# MCS/QCS145 C

## QCS145 C 1xHAL-P38-120W

1, HalogenA PAR38, 120 W

Professional surface mounted downlights complimenting the family of the 145 range. Complete with a very efficient highly-polished reflector in silver aluminium finish. Suitable for PAR reflector halogen, the range comes with a standard white decorative plastic ring. Accessories are common and interchangeable for the entire 145 range. Colour options upon request.

### Product data

General Information	
Lamp family code	HAL-P38 [HalogenA PAR38]
Gear	-

  

Light Technical	
Number of light sources	1

  

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	120 W

  

Controls and Dimming	
Driver/power unit/transformer	Electronic transformer

  

Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

  

Product Data	
Order product name	QCS145 C 1xHAL-P38-120W
Full product name	QCS145 C 1xHAL-P38-120W
Full product code	910401681080
Order code	01681080
Material Nr. (12NC)	910401681080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291993476
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291993476

# MCS/QCS145 C

## Dimensional drawing

