



FBH059

FBH059 2xPL-C/2P18W I WH

2 pcs - MASTER PL-C 2 Pin - 18 W - Inductive - White


The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Product data

General Information	
Number of light sources	2 [2 pcs]
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Lamp power	18 W
Compensation circuit	Inductive
Gear	CONV [Conventional]
Country version	NO [Norway]
Operating and Electrical	
Input voltage	220 V
Input frequency	50 Hz
Approval and Application	
Ingress protection code	IP20 [Finger-protected]



Product Data	
Full product code	910401945280
Order product name	FBH059 2xPL-C/2P18W I WH
Order code	910401945280
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910401945280
Net weight (piece)	1.999 kg

Dimensional drawing



FBH059

Photometric data



IFGU1_FBH059 2xPL-C2P18W.EPS

IFPC1_FBH059 2xPL-C2P18W.EPS

