



# Tunnelite SGX320

## SGX320 1xSON-T400W 220V-50Hz CP

1, SON-T, 400 W, Asymmetrical

Tunnel luminaire SGX320 suitable for use with SON-T 150-400W high pressure sodium vapour lamps.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optic type outdoor	Asymmetrical
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	400 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	SGX320 1xSON-T400W 220V-50Hz CP
Full product name	SGX320 1xSON-T400W 220V-50Hz CP
Full product code	910401960780
Order code	910401960780
Material Nr. (12NC)	910401960780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Tunnelite SGX320

### Dimensional drawing

