



Broadway SGP268

SGP268 SON-T400W 220V-50Hz GB SI

SON-T, 400 W, 220 V, 50 Hz, Glass bowl/cover, Silver

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

Product data

| General Information | |
|--------------------------|------------------|
| Lamp family code | SON-T [SON-T] |
| Cap-Base | E40 [E40] |
| Gear | SGR [SON gear] |
| Light Technical | |
| Number of light sources | 1 |
| Optical cover type | Glass bowl/cover |
| Optic type outdoor | Open T-POT |
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Power Consumption | 400 W |
| Mechanical and Housing | |
| Housing Color | Silver |

| Approval and Application | |
|---------------------------------|---|
| Ingress protection code | IP43/66 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof] |
| Product Data | |
| Order product name | SGP268 SON-T400W 220V-50Hz GB SI |
| Full product name | SGP268 SON-T400W 220V-50Hz GB SI |
| Full product code | 910401962980 |
| Order code | 910401962980 |
| Material Nr. (12NC) | 910401962980 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Broadway SGP268

Dimensional drawing

