



# Tango MMF383

## SMF383 SON-T400W 220V-50Hz

SON-T, 400 W

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

### Product data

| General Information |                |
|---------------------|----------------|
| Lamp family code    | SON-T [SON-T]  |
| Cap-Base            | E40 [E40]      |
| Gear                | SGR [SON gear] |

  

| Light Technical         |   |
|-------------------------|---|
| Number of light sources | 1 |
| Optic type outdoor      | - |

  

| Operating and Electrical |       |
|--------------------------|-------|
| Input Voltage            | 220 V |
| Line Frequency           | 50 Hz |
| Power Consumption        | 400 W |

  

| Mechanical and Housing |   |
|------------------------|---|
| Housing Color          | - |

| Approval and Application |  |
|--------------------------|--|
| Ingress protection code  | IP65 [Dust penetration-protected, jet-proof] |

  

| Product Data                    |                            |
|---------------------------------|----------------------------|
| Order product name              | SMF383 SON-T400W 220V-50Hz |
| Full product name               | SMF383 SON-T400W 220V-50Hz |
| Full product code               | 910401965180               |
| Order code                      | 910401965180               |
| Material Nr. (12NC)             | 910401965180               |
| Numerator - Quantity Per Pack   | 1                          |
| Numerator - Packs per outer box | 1                          |

# Tango MMF383

## Dimensional drawing

